

3M™ Fibrlok™ 250µm Fiber Splice 2540G


Description

3M™ Fibrlok™ 250µm Fiber Splice helps enable fast, easy splicing of 250µm singlemode fiber in Fiber-to-the-Premises (FTTP) installations. It can also be used in multimode LAN installations where 250µm coated fiber is spliced. This low-loss reliable splice can be installed by non-specialized technicians.




3M™ Fibrlok™ 250 µm Fiber Splice

Cross-sectional view of actuated splice



Before actuation



After actuation

After the fiber is inserted, the assembly tool depresses the activator cap to align and lock the fibers in place.

Applications

- Inside or outside buildings
- Fiber closures and terminals
- FTTP drop cables



3M™ Fibrlok™ Splicing Tool

A fraction of the Tooling Cost

The simple, rugged 3M™ Fibrlok™ Splicing Tool is inexpensive and portable. It requires no electrical power and can be used in any environment. Several crews can be equipped for less than the cost of a single fusion splicer.

Features	Benefits
Low loss and back reflection	Reliable high-yield splices
Simple splicing process	Increased installation rate
Strong fiber retention	Prevents fiber movement for stable performance
Superior matching gel	Maintains quality of transmission over time
Rugged portable splice tool	Low expense to equip crews
Small size splice	Fits into most fusion splice trays

3M™ Fibrlok™ 250µm Fiber Splice 2540G

Specifications	
Fiber Type	125µm fiber, 250µm coating
Dimensions	4mm x 4mm x 36mm (0.16" x 0.16" x 1.42")
Operating temperature	-40°C to 75°C (-40°F to 167°F)
Pull out strength	4.4N (1.0 lbf) minimum
Mean Insertion loss	<0.1dB mean
Wavelengths	1310nm, 1490nm, 1550nm, 1625nm
Reflection	< -40dB typical

Ordering Information

Product Number	Description	Pkg
2540G	Fibrlok 250µm Fiber Splice	5/pkg, 60 MOQ
2504G	Fibrlok 250µm Assembly Tool	1/pkg
2559	Fibrlok Splice Kit	1/pkg
2559-C	Fibrlok Splice Kit with Cleaver	1/pkg
2534	Fiber Cleaver	1/pkg

3M and Fibrlok are trademarks of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 12 months from the date of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether indirect, special, incidental or consequential regardless of the legal theory asserted.



Communication Markets Division 3M Telecommunications

6801 River Place Blvd.
Austin, TX 78726-9000
800/426 8688
Fax 800/626 0329
www.3MTelecommunications.com

Please recycle. Printed in USA.
© 3M 2007. All rights reserved.
80-6113-1563-3