

PROTECTION PRODUCTS

Description

TClamp®2512N and TClamp3312N are specifically designed to provide secondary surge and ESD protection for Ethernet and telecom interfaces. They integrate low capacitance, surge-rated steering diodes with a high power transient voltage suppressor (TVS) to provide up to 120A ($t_p=8/20\mu s$) of lightning surge protection. Capacitance is limited to 8pF maximum from line-to-line to ensure correct signal transmission on high-speed lines.

TClamp2512N and TClamp3312N are in a 10-pin SLP2626P10 package measuring 2.6 x 2.6 x 0.60mm. Leads are spaced at a pitch of 0.5mm and are finished with lead-free NiPdAu. They may be used to meet Telcordia GR-1089-CORE short-haul (intra-building) surge requirements and are particularly well suited for applications where board space is at a premium such as integrated connectors/magnetics and carrier class Ethernet equipment.

Features

- Transient Protection to
 - ♦ Bellcore 1089 (Intra-Building) 120A (8/20 μs)
 - ♦ IEC 61000-4-2 (ESD) 30kV (Air), 30kV (Contact)
 - ♦ IEC 61000-4-4 (EFT) 4kV (5/50ns)
 - ♦ IEC 61000-4-5 (Lightning) 120A (8/20 μs)
- Small SLP package saves board space
- Working Voltage Options: 2.5V and 3.3V
- Low Capacitance: 8pF Maximum (Line-to-Line)
- Low Dynamic Resistance
- Solid-State Silicon-Avalanche Technology


Mechanical Characteristics

- SLP2626P10 Package
- Nominal Dimensions: 2.6 x 2.6 x 0.60mm
- Pb-Free, Halogen Free, RoHS/WEEE Compliant
- Lead Finish: matte NiPdAu
- Molding Compound Flammability Rating: UL 94V-0
- Marking : Marking Code + Date Code
- Packaging : Tape and Reel


Applications

- 10/100/1000 Ethernet
- Integrated magnetics
- Access Equipment
- Central Office Equipment
- Customer Premise Equipment

Nominal Dimensions (mm)



Schematic and Pin Configuration



Absolute Maximum Ratings

Rating	Symbol	Value	Units
Peak Pulse Power (tp = 8/20μs)	P _{PK}	2300	W
Peak Pulse Current (tp = 8/20μs)	I _{PP}	120	A
ESD per IEC 61000-4-2 (Contact) ^{(1), (3)}	V _{ESD}	±30	kV
Operating Temperature	T _J	-40 to +85	°C
Storage Temperature	T _{STG}	-55 to +150	°C

Electrical Characteristics (T=25°C unless otherwise specified)

TClamp2512N						
Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Reverse Stand-Off Voltage	V _{RWM}	-40°C to 85°C			2.5	V
Punch-Through Voltage	V _{PT}	I _{PT} = 2μA Line 1 or Line 2 to Center Tab	2.7		4.5	V
Reverse Leakage Current	I _R	V _{RWM} = 2.5V	T = 25°C	0.01	0.100	μA
			T = 85°C	0.02	0.250	μA
Clamping Voltage ⁽²⁾	V _C	I _{PP} = 100A, tp = 8/20μs Line 1 to Line 2		14.5	18	V
Dynamic Resistance ^{(3), (4)}	V _{BO}	tp = 0.2/100ns (TLP) Line 1 to Line 2			0.12	Ohms
Junction Capacitance	C _J	V _R = 0V, f = 1MHz Line 1 to Line 2		5	8	pF
		V _R = 0V, f = 1MHz Line 1 or Line 2 to Center Tab		10	15	pF

Notes:

(1): ESD Gun return path to Ground Reference Plane (GRP)

(2): Measured using an 8/20us constant current source waveform.

(3): Transmission Line Pulse Test (TLP) Settings: tp = 100ns, tr = 0.2ns, I_{TLP} and V_{TLP} averaging window: t₁ = 70ns to t₂ = 90ns.

(4): Dynamic resistance calculated from I_{TLP} = 4A to I_{TLP} = 16A

Absolute Maximum Ratings

Electrical Characteristics (T=25°C unless otherwise specified)

TClamp3312N						
Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Reverse Stand-Off Voltage	V_{RWM}	-40°C to 85°C			3.3	V
Punch-Through Voltage	V_{PT}	$I_{PT} = 2\mu A$ Line 1 or Line 2 to Center Tab	3.5		5.5	V
Reverse Leakage Current	I_R	$V_{RWM} = 3.3V$	T = 25°C	0.01	0.100	μA
			T = 85°C	0.02	0.250	μA
Clamping Voltage ⁽²⁾	V_C	$I_{PP} = 100A$, $t_p = 8/20\mu s$ Line 1 to Line 2		15	20	V
Dynamic Resistance ^{(3), (4)}	V_{BO}	$t_p = 0.2/100ns$ (TLP) Line 1 to Line 2			0.12	Ohms
Junction Capacitance	C_J	$V_R = 0V$, $f = 1MHz$ Line 1 to Line 2		5	8	pF
		$V_R = 0V$, $f = 1MHz$ Line 1 or Line 2 to Center Tab		10	15	pF

Notes:

(1): ESD Gun return path to Ground Reference Plane (GRP)


(2): Measured using an 8/20us constant current source waveform.

(3): Transmission Line Pulse Test (TLP) Settings: $t_p = 100ns$, $t_r = 0.2ns$, I_{TLP} and V_{TLP} averaging window: $t_1 = 70ns$ to $t_2 = 90ns$.


(4): Dynamic resistance calculated from $I_{TLP} = 4A$ to $I_{TLP} = 16A$

Typical Characteristics


Non-Repetitive Peak Pulse Power vs. Pulse Time




Power Derating Curve




Clamping Voltage vs. Peak Pulse Current




TLP Characteristic



Capacitance vs. Reverse Voltage




Capacitance vs. Temperature




Typical Characteristics


ESD Clamping (+8kV Contact per IEC 61000-4-2)



ESD Clamping (-8kV Contact per IEC 61000-4-2)




Outline Drawing - SLP2626P10




- NOTES:
- 1. CONTROLLING DIMENSIONS ARE IN MILLIMETERS (ANGLES IN DEGREES).
 - 2. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.

Land Pattern - SLP2626P10



- NOTES:
- 1. THIS LAND PATTERN IS FOR REFERENCE PURPOSES ONLY. CONSULT YOUR MANUFACTURING GROUP TO ENSURE YOUR COMPANY'S MANUFACTURING GUIDELINES ARE MET.


Marking Example



Notes:

YW = Alphanumeric character Date Code

Tape and Reel Specification



Ordering Information

Part Number	Working Voltage	Qty per 7 Inch Reel
TClamp2512N.TCT	2.5V	3000
TClamp3312N.TCT	3.3V	3000

TransClamp and TClamp are registered trademarks of Semtech Corporation.



IMPORTANT NOTICE

Information relating to this product and the application or design described herein is believed to be reliable, however such information is provided as a guide only and Semtech assumes no liability for any errors in this document, or for the application or design described herein. Semtech reserves the right to make changes to the product or this document at any time without notice. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. Semtech warrants performance of its products to the specifications applicable at the time of sale, and all sales are made in accordance with Semtech's standard terms and conditions of sale.

SEMTECH PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS, OR IN NUCLEAR APPLICATIONS IN WHICH THE FAILURE COULD BE REASONABLY EXPECTED TO RESULT IN PERSONAL INJURY, LOSS OF LIFE OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. INCLUSION OF SEMTECH PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE UNDERTAKEN SOLELY AT THE CUSTOMER'S OWN RISK. Should a customer purchase or use Semtech products for any such unauthorized application, the customer shall indemnify and hold Semtech and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs damages and attorney fees which could arise.

The Semtech name and logo are registered trademarks of the Semtech Corporation. All other trademarks and trade names mentioned may be marks and names of Semtech or their respective companies. Semtech reserves the right to make changes to, or discontinue any products described in this document without further notice. Semtech makes no warranty, representation or guarantee, express or implied, regarding the suitability of its products for any particular purpose. All rights reserved.

© Semtech 2015

Contact Information

Semtech Corporation
200 Flynn Road, Camarillo, CA 93012
Phone: (805) 498-2111, Fax: (805) 498-3804
www.semtech.com