





AA17251



External Dimensions



Frame: Aluminum Alloy
Impeller: Plastic (UL: 94V-0)
Motor Structure: Shaded Pole Induction Motor.
Motor Protection: Impedance Protect.
Lead wire: UL 1015 AWG 18
OPERATING TEMP*: -10°C~70°C
*: -10°C~60°C for fans with sleeve/ball combination bearings.

Specifications(Nominal)


*: Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ○=1B1S ●=Hypro bearing


Frame size (mm)	Model No.	Bearing System Type	Volt. (VAC)	Freq. (Hz)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum		Maximum		*Noise Level (dB/A)	Weight (g)
								AirFlow (CMM)	(CFM)	Pressure (InAq)	(mmAq)		
172x150X51	AA1751HB-AT	◎	115	50/60	0.52/0.47	40.90/36.70	2500/2800	5.546/5.943	196.0/210.0	0.425/0.266	10.795/6.756	52.3/53.0	930
	AA1752HB-AT		230		0.28/0.24	41.90/37.60							

Specifications subject to change without notice.

50Hz



60Hz



*Safety approvals

✓	✓		✓	✓