

**Description:**

19 AWG stranded (7x27) bare copper conductor, gas-injected foam HDPE insulation, double tinned copper braid shield (99% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	19	7x27	BC - Bare Copper	.040

Insulation**Insulation Material:**

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	.180

Outer Shield**Outer Shield Material:**

Layer #	Type	Outer Shield Material	Coverage (%)
1	Braid	TC - Tinned Copper	93
2	Braid	TC - Tinned Copper	93

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cabling

Overall Nominal Diameter: 0.276 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +75°C
UL Temperature Rating:	75°C
Bulk Cable Weight:	50 lbs/1000 ft.
Max. Recommended Pulling Tension:	82 lbs.
Min. Bend Radius (Install)/Minor Axis:	2.750 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes

1694F Coax - Low Loss Serial Digital Coax

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

RG Type: 6/U

Flame Test

UL Flame Test: UL1666 Vertical Shaft

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes - Black only

Suitability - Aerial: Yes - Black only, when supported by a messenger wire

Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 1695A

Electrical Characteristics (Overall)**Nom. Characteristic Impedance:**

Impedance (Ohm)

75

Nom. Inductance:

Inductance (μH/ft)

0.106

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.2

Nominal Velocity of Propagation:

VP (%)

81

Nominal Delay:

Delay (ns/ft)

1.25

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

8.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

1.7

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100 ft.)

1 0.24

3.58 0.45

5 0.54

7 0.62

10 0.72

67.5 1.9

71.5 2.0

88.5 2.2

100 2.4

135 2.8

143 2.9

180 3.3

270 4.0

360 4.7

1694F Coax - Low Loss Serial Digital Coax

540	5.9
720	6.9
750	7.0
1000	8.2
1500	10.4
2000	12.3
2250	13.2
3000	15.6
4500	19.8

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

Other Electrical Characteristic 1:

Impedance tested in accordance with ASTM D-4566 paragraph 43.2, option 2 using a 75 Ohm fixed bridge and termination. 75 +/- 1.5 Ohms

Other Electrical Characteristic 2:

Return Loss tested in accordance with ASTM D-4566 paragraph 45.3, using a 75 Ohm fixed bridge and termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5	850	20
850	4500	15

Sweep Test

Sweep Testing:

100% Sweep tested 5 MHz to 4.5 GHz.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1694F B591000	1,000 FT	54.000 LB	BLACK, MATTE	C	#19 GIFHDLDPPE DBLB FRPVC
1694F G7V1000	1,000 FT	54.000 LB	RED, MATTE	C	QLTHLDFHDLDPPE DBLB FRPVC
1694F G7W1000	1,000 FT	54.000 LB	GREEN, MATTE	C	#19 GIFHDLDPPE DBLB FRPVC
1694F G7X1000	1,000 FT	54.000 LB	BLUE, MATTE	C	#19 GIFHDLDPPE DBLB FRPVC
1694F G7Y1000	1,000 FT	54.000 LB	WHITE, MATTE	C	#19 GIFHDLDPPE DBLB FRPVC
1694F G8L1000	1,000 FT	54.000 LB	ORANGE, MATTE	C	#19 GIFHDLDPPE DBLB FRPVC
1694F G8M1000	1,000 FT	54.000 LB	YELLOW, MATTE	C	#19 GIFHDLDPPE DBLB FRPVC
1694F Z4B1000	1,000 FT	54.000 LB	VIO Z4B	C	#19 GIFHDLDPPE DBLB FRPVC

Notes:

C = CRATE REEL PUT-UP.