

HC/49US (AT49) SMD LOW PROFILE CRYSTAL



11.5 x 4.7 x 4.2 mm

ABLS



RoHS Compliant

Moisture Sensitivity Level (MSL) – This product is Hermetically Sealed and not Moisture Sensitive - MSL = N/A: Not Applicable

FEATURES:

- Suitable for RoHS reflow
- Available for tight stability & extended temperature range

APPLICATIONS:

- Computers, Modems, Microprocessors
- Wireless Applications

STANDARD SPECIFICATIONS:

PARAMETERS


ABRACON P/N	ABLS Series
Frequency	3.579545 MHz to 75 MHz
Operation Mode	AT cut (Fundamental or 3rd OT) or BT cut (See options) 3.579545MHz - 24.0MHz (Fundamental: Standard) 24.01MHz - 75.00MHz (3rd- Overtone: Standard) 24.01MHz - 50.00MHz (Fund. AT or BT: See options)
Operating Temperature	0°C to + 70°C (see options)
Storage Temperature	- 55°C to + 125° C
Frequency Tolerance at +25°C	± 50 ppm max. (see options)
Frequency Stability over the Operating Temp. (Ref to +25°C)	± 50 ppm max. (see options)
Equivalent Series Resistance	See Table 1
Shunt Capacitance C ₀	7pF max.
Load Capacitance C _L	18pF (see options)
Drive Level	1 mW max., 100 µW typical
Aging at 25°C (first year)	± 5ppm max.
Insulation Resistance	500 MΩ min at 100Vdc ± 15V
Spurious Responses	-3dB max.
Drive level dependency (DLD)	from 1 µW to 500 µW (minimum 7 points tested)

TABLE 1: STANDARD ESR

FREQUENCY (MHz)	ESR (Ω) MAX
3.579 - 4.999 (Fund.)	180
5.000 - 5.999 (Fund.)	120
6.000 - 7.999 (Fund.)	100
8.000 - 8.999 (Fund.)	80
9.000 - 9.999 (Fund.)	60
10.000 - 15.999 (Fund.)	50
16.000 - 50.000 (Fund.)	40
24.01 - 31.999 (3rd O/T)	100
32.000 - 75.00 (3rd O/T)	80

OPTIONS & PART IDENTIFICATION:

(Left blank if standard)



* -10 to +60° C only.

** Option A, B, and 0 to +70° C only.


*** Frequency stability ±50ppm, ±100ppm, or ±150ppm only.

Contact ABRACON for tighter frequency stability.

**** For Fundamental BT, frequency stability

± 100ppm max. at -10° C to +60° C only.

ABRACON IS
ISO9001:2008
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale

30332 Esperanza, Rancho Santa Margarita, California 92688

tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

Revised: 04.07.11

11.5 x 4.7 x 4.2 mm



RoHS
Compliant

Technical drawing of a 1.5mm pitch BGA package showing top, side, and cross-sectional views with dimensions in inches and mm.

Top View Dimensions:

- Overall width: 0.500 ± 0.024 (12.7 $\pm$ 0.6)
- Inner width: 0.45 ± 0.006 (11.4 $\pm$ 0.15)
- Height: 0.19 ± 0.006 (4.7 $\pm$ 0.15)

Side View Dimensions:

- Top width: 0.406 max. (10.3)
- Height: 0.16 max. (4.2)
- Bottom thickness: 0.004 max. / 0.000 min. (0.1 max. / 0.0 min.) both sides

Cross-sectional View Dimensions:

- Central hole diameter: $0.024 + .008 / -.004$ (0.6 + 0.2 / -0.1)
- Distance from center to edge: 0.192 ± 0.008 (4.88 $\pm$ 0.2)

Recommended land pattern:

- Land width: 0.22 (5.6)
- Land spacing: 0.374 (9.5)
- Land thickness: 0.083 (2.1)

Dimensions: Inches (mm)

FEEDING (PULL) DIRECTION →

0.3±0.005

1.75±0.1

2.0±0.1

4.0±0.1

1.5±0.1

24.0±0.3

13.0±0.1

5° MAX

4.5±0.1

12±0.1

5.1±0.1

Ø1.5

Ø1.5

25.5+2/-0

2.0

100

Ø330±1


Ø13.0±0.5

2.5

120°

Ø21.0±1

Dimensions: mm



Need a test socket for the ABLS series? To view compatible **PRECISION TEST & BURN-IN SOCKETS for these parts, click here**P/N: AXS-1147-02-02

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO9001:2008
CERTIFIED



ABRACON CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale

30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

Revised: 04.07.11