

DATA LSG, LSH, LPH, LPS, LPV, SMS, PMS, MTG SWITCHES-MOMENTARY ACTION




BENEFITS

- Simple assembly, long life time, short lead time
- Reliable tactile feedback
- Various designs with 1/4 and 1/2 inch are possible with different heights
- Variable colour design and lettering
- Available for through hole and SMD assembly
- Tested to degree of protection IP 40 and IP 67

		LSG//LSH/LPH LPS//LPV	SMS	PMS	MTG	
Electrical data						
Contact material					gold	silver
Switching voltage max.	[V]	12 DC	30 AC / 42 DC	30 AC / 42 DC	max. 24 DC	max. 48 DC
Switching current max.	[mA]	50	50	50	max. 50	max. 125
Rated breaking capacity	[W]		0.12	0.12	0.48	2.40
Lifetime (at rated breaking capacity)		> 10 ⁵	> 10 ⁶	> 10 ⁶	> 10 ⁶	> 10 ⁶
Initial contact resistance, new	[mΩ]	max. 100	< 50	< 50	< 50	< 50
Initial contact resistance, after lifetime	[mΩ]	max. 100	< 150	< 150	< 50	< 50
Insulation resistance	[mΩ]		> 10 ⁸	> 10 ⁸	> 10 ⁸	> 10 ⁸
Contact bounce time	[ms]	typ. 0.1	typ. 0.15	typ. 0.15	typ. 0.1	typ. 0.1
Mechanical data						
Actuating force	IP 40 [N] IP 67 [N]	1.6 ± 0.5	1.8 ± 0.4 2.2 ± 0.4	1.8 ± 0.4 2.2 ± 0.4	2.5 ± 0.5	2.5 ± 0.5
Contact travel	[mm]	0.25 + 0.2/-0.1	0.35 ± 0.1	0.35 ± 0.1	0.45 ± 0.1	0.45 ± 0.1
End stop strength	[N]	50 N/3s	> 100	> 100	> 50	> 50
Lifetime	[operations]	> 10 ⁵	> 10 ⁶	> 10 ⁶	> 10 ⁶	> 10 ⁶
Other data						
Degree of protection		IP 40	IP 40/IP 67	IP 40/IP 67	IP 40	IP 40
Solderability	(CECC 00802 and IEC 68-2-20) (IEC 68-2-20 test Ta, method 1) [°C/s]		IR - Reflow		235 / 2	235 / 2
Soldering heat resistance	(LSH/LSG) IR Reflow [°C/s] (LPV/LPS/LPH) [°C/s]	230 / 30 250 / 5				
	IEC 68-2-20 test Tb, method 1A [°C/s]			260 / 10	260 / 5	260 / 5
	IEC 68-2-20 test Tb, method 2 [°C/s]		350 / 10	350 / 10		
	CECC 00802 classification B [°C/s]		215 / 40			
	CECC 00802 classification C [°C/s]		260 / 10			
Ambient temperature	[°C]	-20 – +70	-40 – +85	-40 – +85	-25 – +85	-25 – +85
Storage temperature	[°C]	-30 – +85	-40 – +85	-40 – +85	-25 – +85	-25 – +85
Cleaning agent proof			Zestron	Zestron		
Flux - proof				given		
Materials						
Sealing membrane IP 67			VMQ		VMQ	
Contact material gold			CuZn -1.5µm Ni + 0.5µm Au		CuZn -3µm Ni +2µm Au	
Contact material silver		*			CuZn -2.5µm Ag passivated	
Terminals		*	CuZn -8µm SnPb			
Socket		*	Thermoplast PA 4.6		Thermoplast PES	
Actuator		*	Thermoplast PPS		Thermoplast PC	
Cover plate		*	X 12CrNi177			

* on request

OVERVIEW LSG, SMS SWITCHES – MOMENTARY ACTION



LSG



SMS



SMS

FEATURES

Degree of protection	IP 40	IP 40	IP 67
PART NUMBER *			
Leads/Overall height			
Gullwing/2.50 mm	1301.9312.xx		
Gullwing/3.10 mm	1301.9313.xx		
Gullwing, short actuator		1241.1600.xx	1241.1606.xx
J-Leads, short actuator		1241.1601.xx	1241.1607.xx
Gullwing, long actuator		1241.1612.xx	1241.1618.xx
J-Leads, long actuator		1241.1613.xx	1241.1619.xx
Packaging			
loose in boxes		11	11
taped and reeled	25	23	23

BUTTON IN VARIABLE HEIGHTS FOR LONG ACTUATORS SMS **

overall height h = 8.50 mm / yellow		0862.8101
h = 9.25 / orange		0862.8102
h = 10.00 mm / red		0862.8103
h = 10.75 mm / blue		0862.8104
h = 11.50 mm / green		0862.8105
h = 12.25 mm / grey		0862.8106
h = 13.00 mm / black		0862.8107
h = 13.75 mm / white		0862.8108
Second key cap***		0862.8226
Dimensions:		Dimensions, Gullwing: Dimensions, J-leads:
Circuit diagram: Solder pads:	Solder pads, Gullwing: Dimensions, J-leads: Overall height h:	

* X in the Part No. must be replaced by the desired version

** Button in variable heights for long actuators must be ordered separately

***Starting with 14.50 mm, additional (second) key caps for midsize (h+6mm) are necessary. Order separately.

Circuit diagrams SMS see page 10 PMS

OVERVIEW PMS SWITCHES—MOMENTARY ACTION



PMS

PMS

FEATURES

Degree of protection

IP 40

IP 67

PART NUMBER *

Models

Short actuator

1241.1602

1241.1608

Long actuator

1241.1614

1241.1620

Height variable

1241.1624. xx

1241.1625. xx

Overall height h (with key cap)/Colour

8.35 mm / yellow

1

1

9.10 mm / orange

2

2

9.85 mm / red

3

3

10.60 mm / blue

4

4

11.35 mm / green

5

5

12.10 mm / grey

6

6

12.85 mm / black

7

7

13.60 mm / white

8

8

Additional key cap¹

Overall height h/Colour

14.35 mm / yellow + black

11

11

15.10 mm / orange + black

21

21

15.85 mm / red + black

31

31

16.60 mm / blue + black

41

41

17.35 mm / green + black

51

51

18.10 mm / grey + black

61

61

18.85 mm / black + black

71

71

19.60 mm / white + black

81






81

Dimensions through hole mounting:

Overall height variable:

Drilling diagram:

Circuit diagram:



* X in the Part No. must be replaced by the desired version

¹ Starting with 14.35 mm the heights are achieved with an additional (second) key cap of black colour