

CATALOG LISTING
1TL84 SERIES CHART 1
PAGE 1 OF 1
REPLACES NO CO-78465
CHECK
REVISIONS
A CO 94431
C ST 24 NOV 99
B 202798
C SL 9 APR 01
CHECK
KAG 23 JUN 94
DLT 10 JUN 94
DRAWN
RASTER

MICRO SWITCH
FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL
FED. MFG CODE 91929

SWITCH - TOGGLE

CATALOG LISTING
1TL84 SERIES
CHART 1


AVAILABLE
LOCKING
COMBINATIONS
FOR CONFIGURATION
SEE LETTERED DETAILS

CATALOG
LISTING
6

CIRCUIT MADE
WITH TOGGLE LEVER IN
KEYWAY
SIDE
(1-2)
CENTER
(1-2)
OPPOSITE
KEYWAY
(2-3)



MILITARY RATING (AMPS)
RESISTIVE LOAD
DC VOLTS
28 125 250
AC VOLTS
125 250
LAMP LOAD
28 VDC
125 VAC
INDUCTIVE LOAD
28 VDC
125 VAC

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



R	ITL84-1	ON	OFF	ON
R	ITL84-2	OFF	NONE	ON
R	ITL84-3	ON	NONE	ON
R	ITL84-2I	NONE	OFF	ON
R	ITL84-3I	NONE	ON	ON
S	ITL84-4	MOM OFF	NONE	ON
R	ITL84-5	MOM ON	OFF	ON
S	ITL84-6	MOM ON	NONE	OFF
R	ITL84-7	MOM ON	OFF	MOM ON
S	ITL84-8	MOM ON	NONE	ON
T	ITL84-5I	NONE	ON	MOM ON
S	ITL84-6I	MOM ON	OFF	NONE
S	ITL84-8I	MOM ON	ON	NONE

20	75	5	15	6	5	3	15	10
(REFER TO L191 FOR UL RATING)								
15	75	5	15	6	4	2	10	7
(REFER TO L192 FOR UL RATING)								



- NOTES
- 1 - SWITCHES ARE CAPABLE OF WITHSTANDING A TEMPERATURE OF 160°F CONTINUOUSLY AT FULL RATED LOAD
 - 2 - CIRCUIT DESIGNATION AND MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
 - 3 - FURNISHED UNASSEMBLED
 - 4 - FOR TERMINAL COVER, SEE MICRO SWITCH CATALOG LISTING 5PA7
 - 5 - KEYWAY SHOWN ON LEFT SIDE
 - 6 - SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE OF TOGGLE LOCKING. SEE CHART FOR AVAILABLE LOCKING COMBINATIONS
 - 7 - APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS

THIRD ANGLE PROJECTION
SCALE FULL
DO NOT SCALE PRINT
TOLERANCES
APPLY TO DESIGN UNITS CONVERSIONS ARE ONLY FOR REFERENCE UNLESS NOTED TOLERANCES ARE:
NO PLACES X
ONE PLACE X X
TWO PLACES X X X
THREE PLACES X X X X
ANGLES
DESIGN UNITS
SI METRIC
US CUSTOMARY
RAW MATERIAL - COMMERCIAL STANDARD
MICRO SWITCH STANDARDS APPLY
DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED
WEIGHT .08 LBS APPROX

CE
15A-125,250 OR 277VAC
1/2HP-125VAC; 1HP-250,277VAC
5A-125VAC "L" CODE L191
CE
10A-125,250 OR 277VAC
1/4HP-125VAC; 1/2HP-250,277VAC
3A-125VAC "L" CODE L192