





REV	DOCUMENT	CHANGED BY	CHECK
A	0038847	PK 11APR08	ASD



1. TERMINALS WILL ACCEPT 6.35mm WIDE QUICK CONNECT RECEPTACLES AND COMPLY WITH EN61058-1 REQUIREMENTS.

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: MM		DRAWN		KSR		07APR08		Honeywell							
OPERATING FORCE: 100gf MAX. DIFFERENTIAL FORCE: RELEASE FORCE: 25gf MIN. FREE POSITION: OPERATING POSITION: 14.7±0.5MM. PRE-TRAVEL: 1.6MM MAX. DIFFERENTIAL TRAVEL: 0.4MM MAX. OVER-TRAVEL: 0.8MM MIN. FULL OVERTRAVEL FORCE:		CONTACT ARRANGEMENT S.P.D.T		TOLERANCES UNLESS NOTED:		CHECK		RJ		07APR08						TITLE SWITCH - BASIC			
		 16(4)A 250V~ 25T125 µ 5E4  16A 1/2HP 125/250VAC		NO PLACE X ± ± ONE PLACE .X ± ± TWO PLACE .XX ± ± 0.40 THREE PLACE .XXX ± ± ANGLES X ± ± 2°		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		SIZE B	TYPE I								
				THIRD ANGLE PROJECTION 		AutoCAD		SCALE		NTS		SHEET		1 OF 1					