


LOC	DIST	REVISIONS			
		P	LTR	DATE	DWN
FT	0		U	REVISED PER 0G3B-0095-05	3/31/05

D

C


B

A



- 1 0.76um[.000030] MIN GOLD FOR A LENGTH OF 5.08[.200] MIN FROM MATING END WITH GOLD FLASH ON REMAINDER, ALL OVER 1.27um[.000050] MIN NICKEL.
- 2 POSTS ARE SEMI-AUTOMATICALLY WIREABLE AND WILL ACCOMODATE 3 TERMINATIONS.
- 3 #24 AWG MAX WIRE TO BE USED WITH THIS CONNECTOR.
- 4 ALTERNATE DIMENSIONS FOR USE WITH JACK SCREWS.
- 5 2.54um[.000100] MIN TIN-LEAD OVER 1.27um[.000050] MIN NICKEL.
- 6 2.54um[.000100] MIN TIN OVER 1.27um[.000050] MIN NICKEL.

6	0.43 [.017]	16.74 [.659]	0.64x0.64 [.025x.025]	PHENOLIC BLACK	5-205156-9
5	-	20.57 [.810]	0.79x1.57 [.031x.062]	DIALLYL PHTHALATE BLUE	5-205156-8
5	0.43 [.017]	16.74 [.659]	0.64x0.64 [.025x.025]	PHENOLIC BLACK	205156-1
POST FINISH	B	A	POST	BLOCK MATERIAL	PART NUMBER



RECOMMENDED PANEL CUTOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. REIFSNYDER 07 FEB 96	tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		CHK R. STONE 22 FEB 96		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. MCALONIS 22 FEB 96	NAME PIN ASSY, 50 POSITION, AUTOWIREABLE, STD M SERIES	
		PRODUCT SPEC		
MATERIAL SEE CALLOUTS		APPLICATION SPEC	SIZE A2	
FINISH SEE CALLOUTS		WEIGHT -	CAGE CODE 00779	
		CUSTOMER DRAWING	DRAWING NO C=205156	
		SCALE 2:1	SHEET 1 OF 1	
			REV U	