

Technical Data



Performance you can trust



Industrial Cleaner Rapid Dry

Multi-purpose, fast drying, degreaser that leaves no residue.

A specially formulated blend of degreasing solvents designed to remove grease, oil and general workshop grime rapidly from a wide range of surfaces.

Ideal for use where a fast drying non-chlorinated solvent cleaner is required, particularly if a clean residue free surface is essential.

Features

- Extremely powerful cleaning solvent
- Evaporates quickly, dries in seconds and leaves no residue
- Does not contain chlorinated solvents
- Available in convenient aerosol form
- FDA Group 21 CFR 178.3570
- NSF K1 registered – 135883
- DIN V 10517

Directions for Use

- Shake can well and spray from a distance of approximately 15-30 cms
- The spray can may be used at any angle due to 360° valve technology
- Do not smoke during use or spray onto naked flame or any other incandescent material
- For heavier contamination, reapplication may be necessary
- As with all products of this type it is recommended that compatibility with painted or coated surfaces, plastics and rubber be tested prior to use

T +44 (0) 113 232 2600
F +44 (0) 113 232 2740
E customer-service@rocol.com
www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of



BS EN ISO 9001
Certificate No. FM 12448



BS EN ISO 14001
Certificate No. EMS 67596



OHSAS 18001
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers.
There are many factors outside our control or knowledge which affect the use and performance
of our products, for which reason it is given without responsibility.

Technical Data



Performance you can trust

Industrial Cleaner Rapid Dry

Appearance	Colourless liquid
Propellant	CO ₂ (Carbon dioxide)
Solvent	Blend of hydrocarbon and alcohol
Flash Point (PMCC)	<0°C
Density (kg/m³)	0.74 (measured as kg/litre)
Storage	Storage temperature should be kept below 50°C. Storage area should be: out of direct sunlight.
Pack sizes – Part Codes	300 ml – p/c 34131

T +44 [0] 113 232 2600
F +44 [0] 113 232 2740
E customer-service@rocol.com
www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001
Certificate No. FM 12448



BS EN ISO 14001
Certificate No. EMS 67596



OHSAS 18001
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers.
There are many factors outside our control or knowledge which affect the use and performance
of our products, for which reason it is given without responsibility.