Harmony ™ Double and Triple-Headed Push Buttons

Catalog

2011

Schneider Electric™

Improved selection, simplicity and robustness

As a world leader in control and signaling components, Schneider Electric continues to innovate within the Harmony ranges to improve the efficiency of your dialog solutions.

Intended for simple applications, the new double and triple-headed push buttons feature extreme robustness, refined ergonomics, and very simple installation.

Contents

Product advantages ..... p. 4
Selection guide ..... p. 5
References: Harmony XB4, metal bezel ..... p. 6
References: Harmony XB5, plastic bezel ..... p. 8
Characteristics and dimensions: Harmony XB4, metal bezel ..... p. 10
Characteristics and dimensions: Harmony XB5, plastic bezel ..... p. 11
Substitution table (new/old range) ..... p. 12

Make the most of your energy[SM]

> Discover the solution whatever your application

100%
worldwide availability

Complete offer

- Double-headed, double-headed + pilot light, and triple-headed push button versions
- Plastic and metal bezel ranges
- Very flexible offer with complete products as well as sub-assemblies for customer assembly
- Wide choice of push button caps (colors, markings) to meet your requirements

Customization

- Customize the push button by selecting caps with appropriate markings for your specific applications

> Gain in space and simplicity

66%
time savings
when installing a
3-function product

Gain space on your control panels

- Up to 3 functions combined in a single product

Simplicity and speed of installation

- Only one Ø 22 mm hole required for installing a product with up to 3 functions
- Only one installer required: non-rotating head in its cut-out
- Fitting and removal of silicone boots without removing the push button (protection against splashing, etc.)

> Opt for robust products

Tested and certified performance

- 1 million mechanical operations
- Operation down to -25 °C as standard
- Clear, easy-to-read push button cap markings, which are tamperproof due to the use of double injection molding
- High luminosity LED for versions with pilot light

IP66/ IP69K

High degree of protection as standard (without boot)

Conformity to the most demanding standards

- EN/IEC 60947-1, EN/IEC 60947-5-1
- EN/IEC 60947-5-4
- UL 508, CSA C22.2 No. 14
- This product is manufactured in conformity with the European RoHS (Restriction of Hazardous Substances) directive

100 % RoHS

Schneider Electric is committed to reducing the environmental impact of its products

> Selection guide

flush pushes	Double-headed push button (XB4/XB5 ranges)	Double-headed push button + 1 clear central pilot light (XB4/XB5 ranges)	Triple-headed push button (XB4/XB5 ranges)
ads only, caps Plastic / Metal			
ads only, out caps customization) Plastic / Metal			
nplete ducts Plastic / Metal			
flush push and 1 projecting push			
ads only, caps Plastic / Metal			
nplete ducts Plastic / Metal			

Control and signaling units, Ø 22

Harmony™ XB4 metal

Multiple-headed push buttons, spring return

569134

XB4BL73415

569136

ZB4BA7121

569138

ZB4BL7341

569140

XB4BW73731●5

569142

ZB4BW7A1721

569150

ZB4BW7A3741

Double-headed push buttons *(1)*

Screw clamp terminal connections (Schneider Electric anti-retightening system)

Shape of head	Description	Type of contact N/O	Type of contact N/C	Color and marking of caps *(2)*	Reference	Weight kg
Complete units						
	2 pushes (1 flush black + 1 projecting red)	1	1	White “I” on green background White “O” on red background	**XB4BL73415** (n)	0.116
Heads only						
	2 flush black pushes			White background + black background, unmarked	**ZB4BA7120** (n)	0.056
				Black “I” on white background White “O” on black background	**ZB4BA7121** (n)	0.056
				Green background + red background, unmarked	**ZB4BA7340** (n)	0.056
				White “I” on green background White “O” on red background	**ZB4BA7341** (n)	0.056
				Without cap *(3)*	**ZB4BA79** (n)	0.056
	1 flush black push 1 projecting red push			Green background + red background, unmarked	**ZB4BL7340** (n)	0.056
				White “I” on green background White “O” on red background	**ZB4BL7341** (n)	0.056

Double-headed push buttons + 1 white central pilot light block *(1)*

Screw clamp terminal connections (Schneider Electric anti-retightening system)

Shape of head	Description	Type of contact N/O	Type of contact N/C	Color and marking of caps *(2)*	Pilot light voltage V	Reference	Weight kg
Complete units							
Protected™ LED	**1 flush black push 1 projecting red push 1 white central pilot light block**	1	1	White “I” on green background White “O” on red background	24	**XB4BW73731B5** (n)	0.130
					120	**XB4BW73731G5** (n)	0.130
					240	**XB4BW73731M5** (n)	0.130
Heads only *(5)*							
Protected™ LED	**2 flush black pushes 1 clear central pilot light** *(4)*			White background + black background, unmarked		**ZB4BW7A1720** (n)	0.056
				Black “I” on white background White “O” on black background		**ZB4BW7A1721** (n)	0.056
				Green background + red background, unmarked		**ZB4BW7A3740** (n)	0.056
				White “I” on green background White “O” on red background		**ZB4BW7A3741** (n)	0.056
				Black “⬆” on white background White “⇩” on black background		**ZB4BW7A1724** (n)	0.056
				Black “+” on white background Black “–” on white background		**ZB4BW7A1715** (n)	0.056
				Without cap *(3)*		**ZB4BW7A9** (n)	0.056
Protected™ LED	**1 flush black push 1 projecting red push 1 clear central pilot light** *(4)*			Green background + red background, unmarked		**ZB4BW7L3740** (n)	0.056
				White “I” on green background White “O” on red background		**ZB4BW7L3741** (n)	0.056

Heads with black metal bezel

To order, add the suffix **7** to the references selected above. Example: **ZB4BA7120** becomes **ZB4BA71207**.

(1) *For the recommended maximum number of contacts constituting the body (fixing collar + contact) associated with the head, consult our website at www.Schneider-Electric.com.*

(2) These caps are fitted by Schneider Electric and cannot be removed without risk of product damage..

(3) Caps to be ordered separately: see page 7.

(4) Color of centrally positioned pilot light determined by the color of the LED incorporated in the body sub-assembly.

(5) Only for use with bodies that include a Protected LED™ light source.

(n) New

General : page 3 | Characteristics : page 10 | Dimensions : page 10

Control and signaling units, Ø 22
Harmony™ XB4 metal
Multiple-headed push buttons, spring return

Triple-headed push buttons *(1) (2)*
Screw clamp terminal connections (Schneider Electric anti-retightening system)

Shape of head	Description	Type of contact N/O	N/C	N/O	Color and marking of caps *(3)*	Reference	Weight kg
Complete units							
	2 flush black pushes + 1 central projecting red push marked "Stop" in white	1	1	1	White "I" on green background White "II" on green background	**XB4BA731327** (n)	0.128
					Black "➡" on white background White "⇦" on black background	**XB4BA711237** (n)	0.128
Heads only							
	2 flush black pushes + 1 central projecting red push marked "Stop" in white				White "I" on green background White "II" on green background	**ZB4BA73132** (n)	0.056
					White "⇦" on green background White "⇨" on green background	**ZB4BA73133** (n)	0.056
					White "⇧" on green background White "⇩" on green background	**ZB4BA73134** (n)	0.056
					White "+" on green background White "–" on green background	**ZB4BA73135** (n)	0.056
					Black "+" on white background Black "–" on white background	**ZB4BA71115** (n)	0.056
					Black "➡" on white background White "⇦" on black background	**ZB4BA71123** (n)	0.056
					Black "⬆" on white background White "⇩" on black background	**ZB4BA71124** (n)	0.056
					White "⇧" on black background White "⇩" on black background	**ZB4BA72124** (n)	0.056
					Without cap *(4)*	**ZB4BA791** (n)	0.056

569144

XB4BA731327

569146

ZB4BA73133

569148

ZB4BA71124

Specific accessories for multiple-headed push buttons

Description	Background color	Marking	Sold in lots of	Reference	Weight kg
Caps only for clip-on mounting on double or triple-headed push buttons *(5)*	White	Unmarked	10	**ZBA71** (n)	0.010
		"I" black	10	**ZBA7131** (n)	0.010
		"➡" black	10	**ZBA7134** (n)	0.010
		"+" black	10	**ZBA7138** (n)	0.010
	Black	Unmarked	10	**ZBA72** (n)	0.010
		"O" white	10	**ZBA7232** (n)	0.010
		"+" white	10	**ZBA7233** (n)	0.010
		"⇨" white	10	**ZBA7235** (n)	0.010
		"I" white	10	**ZBA7237** (n)	0.010
	Green	Unmarked	10	**ZBA73** (n)	0.010
		"I" white	10	**ZBA7331** (n)	0.010
		"+" white	10	**ZBA7333** (n)	0.010
		"⇧" white	10	**ZBA7335** (n)	0.010
		"II" white	10	**ZBA7336** (n)	0.010
	Red	Unmarked	10	**ZBA74** (n)	0.010
		"O" white	10	**ZBA7432** (n)	0.010
	Yellow	Unmarked	10	**ZBA75** (n)	0.010
	Blue	Unmarked	10	**ZBA76** (n)	0.010
Clear silicone boots *(6)*	For 2 flush pushes	–	10	**ZBA708** (n)	0.055
	For 3 pushes	–	10	**ZBA709** (n)	0.055
	For 1 flush push + 1 projecting push	–	10	**ZBA710** (n)	0.055

540585

ZBA7235

569177

ZBA7331

569178

ZBA7432

540598

ZBA709

Heads with black metal bezel

To order, add the suffix **7** to the references selected above.
Example: **ZB4BA73132** becomes **ZB4BA731327**.

(1) For the recommended maximum number of contacts constituting the body (fixing collar + contact) associated with the head, consult our website at www.Schneider-Electric.com.
(2) Not compatible with high power switching contacts and contacts for printed circuit board.
(3) These caps are fitted by Schneider Electric and cannot be removed without risk of product damage..
(4) Caps to be ordered separately: see accessories on this page.
(5) Can be clipped in at 90° steps, through 360°.
(6) Can be replaced without dismantling the head.

(n) New

General : page 3
Characteristics : page 10
Dimensions : page 10

Control and signaling units, Ø 22
Harmony™ XB5 plastic
Multiple-headed push buttons, spring return

569133
XB5AL73415

569135
ZB5AA7121

569137
ZB5AL7341

569139
XB5AW73731●5

569141
ZB5AW7A1721

569149
ZB5AW7A3741

Double-headed push buttons *(1)*
Screw clamp terminal connections (Schneider Electric anti-retightening system)

Shape of head	Description	Type of contact N/O	Type of contact N/C	Color and marking of caps *(2)*	Reference	Weight kg
Complete units						
	2 pushes (1 flush black + 1 projecting red)	1	1	White “I” on green background White “O” on red background	**XB5AL73415**	0.053
Heads only						
	2 flush black pushes			White background + black background, unmarked	**ZB5AA7120** (n)	0.023
				Black “I” on white background White “O” on black background	**ZB5AA7121** (n)	0.023
				Green background + red background, unmarked	**ZB5AA7340** (n)	0.023
				White “I” on green background White “O” on red background	**ZB5AA7341** (n)	0.023
				Without cap *(3)*	**ZB5AA79** (n)	0.023
	1 flush black push 1 projecting red push			Green background + red background, unmarked	**ZB5AL7340** (n)	0.023
				White “I” on green background White “O” on red background	**ZB5AL7341** (n)	0.023

Double-headed push buttons + 1 white central pilot light block *(1)*
Screw clamp terminal connections (Schneider Electric anti-retightening system)

Shape of head	Description	Type of contact N/O	Type of contact N/C	Color and marking of caps *(2)*	Pilot light voltage V	Reference	Weight kg
Complete units							
Protected™ LED	**1 flush black push 1 projecting red push 1 white central pilot light block**	1	1	White “I” on green background White “O” on red background	24	**XB5 AW73731B5** (n)	0.066
					120	**XB5AW73731G5** (n)	0.066
					240	**XB5AW73731M5** (n)	0.066
Heads only *(5)*							
Protected™ LED	**2 flush black pushes 1 clear central pilot light** *(4)*			White background + black background, unmarked		**ZB5AW7A1720** (n)	0.023
				Black “I” on white background White “O” on black background		**ZB5AW7A1721** (n)	0.023
				Green background + red background, unmarked		**ZB5AW7A3740** (n)	0.023
				White “I” on green background White “O” on red background		**ZB5AW7A3741** (n)	0.023
				Black “⬆” on white background White “⇩” on black background		**ZB5AW7A1724** (n)	0.023
				Black “+” on white background Black “–” on white background		**ZB5AW7A1715** (n)	0.023
				Without cap *(3)*		**ZB5AW7A9** (n)	0.023
Protected™ LED	**1 flush black push 1 projecting red push 1 clear central pilot light** *(4)*			Green background + red background, unmarked		**ZB5AW7L3740** (n)	0.023
				White “I” on green background White “O” on red background		**ZB5AW7L3741** (n)	0.023

(1) *For the recommended maximum number of contacts constituting the body (fixing collar + contact) associated with the head, consult our website at www.Schneider-Electric.com.*
(2) These caps are fitted by Schneider Electric and cannot be removed without risk of product damage..
(3) Caps to be ordered separately: see page 9.
(4) Color of centrally positioned pilot light determined by the color of the LED incorporated in the body sub-assembly.
(5) Only for use with bodies that include a Protected LED™ light source.

(n) New

General : page 3
Characteristics : page10
Dimensions : page 10

Control and signaling units, Ø 22
Harmony™ XB5 plastic
Multiple-headed push buttons, spring return

Triple-headed push buttons *(1) (2)*
Screw clamp terminal connections (Schneider Electric anti-retightening system)

Shape of head	Description	Type of contact N/O	N/C	N/O	Color and marking of caps *(3)*	Reference	Weight kg
Complete units							
	2 flush black pushes + 1 central projecting red push marked "Stop" in white	1	1	1	White "I" on green background White "II" on green background	**XB5AA731327** (n)	0.063
					Black "➡" on white background White "⇦" on black background	**XB5AA711237** (n)	0.063
Heads only							
	2 flush black pushes + 1 central projecting red push marked "Stop" in white				White "I" on green background White "II" on green background	**ZB5AA73132** (n)	0.023
					White "⇦" on green background White "⇨" on green background	**ZB5AA73133** (n)	0.023
					White "⇧" on green background White "⇩" on green background	**ZB5AA73134** (n)	0.023
					White "+" on green background White "–" on green background	**ZB5AA73135** (n)	0.023
					Black "+" on white background Black "–" on white background	**ZB5AA71115** (n)	0.023
					Black "➡" on white background White "⇦" on black background	**ZB5AA71123** (n)	0.023
					Black "⬆" on white background White "⇩" on black background	**ZB5AA71124** (n)	0.023
					White "⇧" on black background White "⇩" on black background	**ZB5AA72124** (n)	0.023
					Without cap *(4)*	**ZB5AA791** (n)	0.023

569143

XB5AA731327

569145

ZB5AA73133

569147

ZB5AA71124

Specific accessories for multiple-headed push buttons

Description	Background color	Marking	Sold in lots of	Reference	Weight kg
Caps only for clip-on mounting on double- or triple-headed push buttons *(5)*	White	Unmarked	10	**ZBA71** (n)	0.010
		"I" black	10	**ZBA7131** (n)	0.010
		"⬆" black	10	**ZBA7134** (n)	0.010
		"+" black	10	**ZBA7138** (n)	0.010
	Black	Unmarked	10	**ZBA72** (n)	0.010
		"O" white	10	**ZBA7232** (n)	0.010
		"+" white	10	**ZBA7233** (n)	0.010
		"⇩" white	10	**ZBA7235** (n)	0.010
		"I" white	10	**ZBA7237** (n)	0.010
	Green	Unmarked	10	**ZBA73** (n)	0.010
		"I" white	10	**ZBA7331** (n)	0.010
		"+" white	10	**ZBA7333** (n)	0.010
		"⇧" white	10	**ZBA7335** (n)	0.010
		"II" white	10	**ZBA7336** (n)	0.010
	Red	Unmarked	10	**ZBA74** (n)	0.010
		"O" white	10	**ZBA7432** (n)	0.010
	Yellow	Unmarked	10	**ZBA75** (n)	0.010
	Blue	Unmarked	10	**ZBA76** (n)	0.010
Clear silicone boots *(6)*	For 2 flush pushes	–	10	**ZBA708** (n)	0.055
	For 3 pushes	–	10	**ZBA709** (n)	0.055
	For 1 flush push + 1 projecting push	–	10	**ZBA710** (n)	0.055

540585

ZBA7235

569177

ZBA7331

569178

ZBA7432

540598

ZBA709

(1) For the recommended maximum number of contacts constituting the body (fixing collar + contact) associated with the head, consult our website at www.Schneider-Electric.com.
(2) Not compatible with high power switching contacts and contacts for printed circuit board.
(3) These caps are fitted by Schneider Electric and cannot be removed without risk of product damage..
(4) Caps to be ordered separately: see accessories on this page.
(5) Can be clipped in at 90° steps, through 360°.
(6) Can be replaced without dismantling the head.

(n) New

General : page 3
Characteristics : page 10
Dimensions : page 10

Control and signaling units, Ø 22

Harmony™ XB4 metal

Multiple-headed push buttons, spring return

Characteristics *(1)*

Protective treatment, standard version			"TH" treatment (tropical finish)
Ambient air temperature around the device	Storage	°C	- 40…+ 70
	Operation	°C	- 25…+ 70: LED and neon bulb versions
Electric shock protection	According to IEC 61140		Class I
Degree of protection	Conforming to IEC 60529		IP 66, IP 69 K
	Conforming to UL and NEMA		Type 4X and 13, unless otherwise stated
Mechanical shock protection	Conforming to IEC 50102		IK 06
Conforming to standards			EN/IEC 60947-1, EN/IEC 60947-5-1, EN/IEC 60947-5-4, EN/IEC 60947-5-5, UL 508, CSA C22-2 n° 14
Mechanical durability *(2)*			1 million of operating cycles

(1) For other technical characteristics, please consult "Control and signaling components" catalog.
(2) Actual product life will vary based on electrical load, duty cycle, application, and environmental conditions.

Dimensions (mm)

Multiple-headed push buttons (double or triple), spring return

XB4 BL73415, XB4 BW73731●5



e: clamping thickness: 1 to 6 mm

XB4 BA731327, XB4 BA711237



e: clamping thickness: 1 to 6 mm

Common face view



Heads for double-headed, spring return push buttons

ZB4BA712● , ZB4BA734●, ZB4BA79



ZB4BL734●



Common face view



ZB4BA712●, ZB4BA734●, ZB4BA79 + boot ZBA708



ZB4BL734● + boot ZBA710



Common face view



Heads for triple-headed, spring return push buttons

ZB4BA7313●, ZB4BA711●●, ZB4BA72124, ZB4BA791





ZB4BA7313●, ZB4BA711●●, ZB4BA72124, ZB4BA791 + boot ZBA709





Heads for double-headed push buttons + central pilot light

ZB4BW7A374●, ZB4BW7A17●●, ZB4BW7A9



ZB4BW7L374●



Common face view



ZB4BW7A374●, ZB4BW7A17●●, ZB4BW7A9 + boot ZBA708



ZB4BW7L374● + boot ZBA710



Common face view



Control and signaling units, Ø 22

Harmony™ XB5 plastic

Multiple-headed push buttons, spring return

Characteristics *(1)*

Protective treatment, standard version			"TH" treatment (tropical finish)
Ambient air temperature around the device	Storage	**°C**	- 40…+ 70
	Operation	**°C**	- 25…+ 70: LED and neon bulb versions
Electric shock protection	Conforming to IEC 61140		Class I
Degree of protection	Conforming to IEC 60529		IP 66, IP 69 K
	Conforming to NEMA		NEMA Type 4X and 13, unless otherwise stated
Conforming to standards			EN/IEC 60947-1, EN/IEC 60947-5-1, EN/IEC 60947-5-4, EN/IEC 60947-5-5, UL 508, CSA C22-2 n° 14
Mechanical durability *(2)*			1 million of operating cycles

(1) For other technical characteristics, please consult "Control and signaling components" catalog.
(2) Actual product life will vary based on electrical load, duty cycle, application, and environmental conditions.

Dimensions (mm)

Multiple-headed push buttons (double or triple), spring return

XB5AL73415, XB5AW73731●5



e: clamping thickness: 1 to 6 mm

XB5AA731327, XB5AA711237



e: clamping thickness: 1 to 6 mm

Common face view



Heads for double-headed, spring return push buttons

ZB5AA712●, ZB5AA734●, ZB5AA79



ZB5AL734●



Common face view



ZB5AA712●, ZB5AA734●, ZB5AA79 + boot ZBA708



ZB5AL734● + boot ZBA710



Common face view



Heads for triple-headed, spring return push buttons

ZB5AA7313●, ZB5AA711●●, ZB5AA72124, ZB5AA791





ZB5AA7313●, ZB5AA711●●, ZB5AA72124, ZB5AA791 + boot ZBA709





Heads for double-headed push buttons + central pilot light

ZB5AW7A374●, ZB5AW7A17●●, ZB5AW7A9



ZB5AW7L374●



Common face view



ZB5AW7A374●, ZB5AW7A17●●, ZB5AW7A9 + boot ZBA708



ZB5AW7L374● + boot ZBA710



Common face view



> Substitution table

Product type	Old version	New version IP66 only	Notes
Plastic head Double-headed pushbutton	ZB5 AA8112	ZB5 AA7120	
	ZB5 AA8212	ZB5 AA7121	
	ZB5 AA8134	ZB5 AA7340	
	ZB5 AA8234	ZB5 AA7341	
	ZB5 AL8334	ZB5 AL7340	
	ZB5 AL8434	ZB5 AL7341	
	ZB5 AL8312		equivalent: ZB5AL7340 or ZB5AA7120
	ZB5 AL8412		equivalent: ZB5AL7341 or ZB5AA7121
		ZB5 AA79	new function
	ZB5 AA9112	ZB5 AA7120	
	ZB5 AA9212	ZB5 AA7121	
	ZB5 AA9134	ZB5 AA7340	
	ZB5 AA9234	ZB5 AA7341	
	ZB5 AL9334	ZB5 AL7340	
	ZB5 AL9434	ZB5 AL7341	
	ZB5 AL9312		equivalent: ZB5AL7340 or ZB5AA7120
	ZB5 AL9412		equivalent: ZB5AL7341 or ZB5AA7121
		ZB5 AA79	new function
Plastic head Double-headed pushbutton + central pilot light	ZB5 AW811723	ZB5 AW7A1720	
	ZB5 AW821723	ZB5 AW7A1721	
	ZB5 AW813743	ZB5 AW7A3740	
	ZB5 AW823743	ZB5 AW7A3741	
	ZB5 AW812743		equivalent: ZB5AW7A3740
	ZB5 AW822743		equivalent: ZBAW77A3741
	ZB5 AW833743	ZB5 AW7L3740	
	ZB5 AW843743	ZB5 AW7L3741	
	ZB5 AW831723		equivalent: ZB5AW7L3740 or ZB5AW7A1720
	ZB5 AW841723		equivalent: ZB5AW7L3741 or ZB5AW7A1721
	ZB5 AW832743		equivalent: ZB5AW7L3740
	ZB5 AW842743		equivalent: ZB5AW7L3741
		ZB5 AW7A1724	new function
		ZB5 AW7A1715	new function
		ZB5 AW7A9	new function
Plastic head Triple-headed pushbutton		ZB5 AA73132	new function
		ZB5 AA73133	new function
		ZB5 AA73134	new function
		ZB5 AA73135	new function
		ZB5 AA71115	new function
		ZB5 AA71123	new function
		ZB5 AA71124	new function
		ZB5 AA72124	new function
		ZB5 AA791	new function
Complete plastic bezel product 	XB5 AL845	XB5 AL73415	version IP66
		XB5 AA731327	new function
		XB5 AA711237	new function
	XB5 AW84B5	XB5 AW73731B5	
	XB5 AW84G5	XB5 AW73731G5	
	XB5 AW84M5	XB5 AW73731M5	
	XB5 AL945	XB5 AL73415	

Product type	Old version	New version	Notes
Silicone boot 	ZBW008	ZBA710	
	ZBW008F	ZBA708	
	ZBW008W	ZBA708	
		ZBA709	new function

Product type	Old version	New version IP66 only	Notes
Metal head Double-headed pushbutton 	ZB4 BA8112	ZB4 BA7120	
	ZB4 BA8212	ZB4 BA7121	
	ZB4 BA8134	ZB4 BA7340	
	ZB4 BA8234	ZB4 BA7341	
	ZB4 BL8334	ZB4 BL7340	
	ZB4 BL8434	ZB4 BL7341	
	ZB4 BL8312		equivalent: ZB4BL7340 or ZB4BA7120
	ZB4 BL8412		equivalent: ZB4BL7341 or ZB4BA7121
		ZB4 BA79	new function
	ZB4 BA9112	ZB4 BA7120	
	ZB4 BA9212	ZB4 BA7121	
	ZB4 BA9134	ZB4 BA7340	
	ZB4 BA9234	ZB4 BA7341	
	ZB4 BL9334	ZB4 BL7340	
	ZB4 BL9434	ZB4 BL7341	
	ZB4 BL9312		equivalent: ZB4BL7340 or ZB4BA7120
	ZB4 BL9412		equivalent: ZB4BL7341 or ZB4BA7121
		ZB4 BA79	new function
Metal head Double-headed pushbutton + central pilot light 	ZB4 BW811723	ZB4 BW7A1720	
	ZB4 BW821723	ZB4 BW7A1721	
	ZB4 BW813743	ZB4 BW7A3740	
	ZB4 BW823743	ZB4 BW7A3741	
	ZB4 BW812743		equivalent: ZB4BW7A3740
	ZB4 BW822743		equivalent: ZB4BW7A3741
	ZB4 BW833743	ZB4 BW7L3740	
	ZB4 BW843743	ZB4 BW7L3741	
	ZB4 BW831723		equivalent: ZB4 BW7L3740 or ZB4 BW7A1720
	ZB4 BW841723		equivalent: ZB4 BW7L3741 or ZB4 BW7A1721
	ZB4 BW832743		equivalent: ZB4BW7L3740
	ZB4 BW842743		equivalent: ZB4 BW7L3741
		ZB4 BW7A1724	new function
		ZB4 BW7A1715	new function
		ZB4 BW7A9	new function
Metal head Triple-headed pushbutton 		ZB4 BA73132	new function
		ZB4 BA73133	new function
		ZB4 BA73134	new function
		ZB4 BA73135	new function
		ZB4 BA71115	new function
		ZB4 BA71123	new function
		ZB4 BA71124	new function
		ZB4 BA72124	new function
		ZB4 BA791	new function
Complete metal bezel product 	XB4 BL845	XB4 BL73415	
		XB4 BA731327	new function
		XB4 BA711237	new function
	XB4 BW84B5	XB4 BW73731B5	
	XB4 BW84G5	XB4 BW73731G5	
	XB4 BW84M5	XB4 BW73731M5	
	XB4 BL945	XB4 BL73415	

Schneider Electric USA, Inc.

8001 Knightdale Blvd.
Knightdale, NC 27545
1-888-SquareD
1-888-778-2733

www.us.schneider-electric.com

Schneider Electric™, Harmony™, and Protected LED™ are trademarks or registered trademarks of Schneider Electric and/or its affiliates in the United States and/or other countries. Other marks used herein may be the property of their respective owners.

The information and dimensions in this catalog are provided for the convenience of our customers. While this information is believed to be accurate, Schneider Electric reserves the right to make updates and changes without prior notification and assumes no liability for any errors or omissions.

9001CT1101 03/2011 © 2011 Schneider Electric. All Rights Reserved.