

### F-3153XP

#### Electrical Specifications (@25C)

1. Maximum Power: 7.5 VA
2. Primary: Series: 230V@50/60 Hz  
Parallel: 115V@50/60Hz
3. Secondary: Series: 30.0V CT @ 0.250 Amps  
Parallel: 15.0V CT @ 0.500 Amps

#### Description:

The F-3153XP is part of a wide selection of plug-in types that meet the needs of PC boards and solid state power supply design. This transformer can satisfy power as well as control and instrumentation applications.

#### Construction:

Wound on a single channel nylon bobbin. Materials are UL recognized, Class B (130° C) rated.

#### Safety:

These products are 100% hipot tested with an insulation of 1500V between primary and secondary windings.

#### Dimensions:

Units: In inches

| A     | B     | C     | D     | E    | F     | G     |
|-------|-------|-------|-------|------|-------|-------|
| 1.625 | 2.812 | 1.437 | 1.875 | .250 | 1.312 | 2.375 |


Mounting holes: 0.187 in.

Pin length: 0.187 in.

Pin size: 0.20 x .041 in.

Weight: 11.0 oz

#### Schematic:



Primary: Series - 1 to 4, Jumper 2 to 3  
Parallel - 1 to 4, Jumper 1 to 3 and 2 to 4

Secondary: Series - 5 to 8, Jumper 6 to 7  
Parallel - 5 to 8, Jumper 5 to 7 and 6 to 8

**RoHS Compliance:** As of manufacturing date February 2005, all standard products meet the requirements of 2011/65/EU, known as the RoHS initiative.

\*Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics website for the most current version. For soldering and washing information please see <http://www.triadmagnetics.com/faq.html>

