



Pos.	$L \pm 0.3$	PART NUMBER	
1	2.54	827 871-1	2
2	7.62		-2
3	12.70		-3
4	17.78		-4
5	22.86		-5
6	27.94		-6
7	33.02		-7
8	38.10		-8
9	43.18		-9
10	48.26	1-	0
11	53.34	1-	1
12	58.42	1-	2
13	63.50	1-	3
14	68.58	1-	4
15	73.66	1-	5
16	78.74	1-	6
17	83.82	1-	7
18	88.90	1-	8
19	93.98	1-	9
20	99.06	2-	0
21	104.14	2-	-1
22	109.22	2-	-2
23	114.30	2-	-3
24	119.38	2-	-4
25	124.46	2-	-5
26	129.54	2-	-6
27	134.62	2-	-7
28	139.70	2-	-8
29	144.78	2-	-9
30	149.86	3-827 871-0	

CONTACT PIN	CuSn	
PIN HOUSING	PBT-GV	GREEN
DESCRIPTION	MATERIAL	COLOR FINISH



1	STECKSEITE:IM BEREICH "F" 0.8μm GOLD ÜBER 1.27 μm NICKEL LÖTSEITE: 2.5—5 μm ZINN ÜBER 1.27 μm NICKEL
2	OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
3	OBSOLETE

DIMENSIONS:		DWN	R.JÄGER	18.05.81	MATERIAL	—		FINISH	—						
mm		CHK	BÖCK	—	TE Connectivity										
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	—	—											
±0.2 mm		PRODUCT SPEC			NAME AMPMODU I PIN HEADER,PITCH 5.08 AMPMODU I STIFTLEISTE,RASTER 5.08										
0 PLC ± —		—													
1 PLC ± —		APPLICATION SPEC			SIZECAGE CODEDRAWING NORESTRICTED TO										
2 PLC ± —															
3 PLC ± —		—			A400779C-827871—										
4 PLC ± —															
ANGLES ± —		WEIGHT			—										
		CUSTOMER DRAWING								SCALE	4:1	SHEET	1 of 1	REV	H