




PRODUCT NUMBER
SEE TABLE




SEE SHEET 3 FOR
LOCATOR/HOLDDOWN
VARIATIONS

.014 [0.36]
AT TIPS



mat'l. code				surface		tolerance		projection		product family			
-				ISO 1302 ✓		ISO 406 ISO 1101				RIBCAGE			
ltr		ecn no		dr		date		tolerances unless otherwise specified		title			
L		J10329		CRG		6/6/01		angles		.XX±.01/0.3			
M		M05-0123		MHT		6/6/05		linear		.XXX±.005/0.13			
N		M06-0225		ERE		06/12/06		0°±2°		.XXXX±.0020/0.051		scale 4:1	
P		M06-0370		MHT		9/26/06		dr		M. CORNMAN		6/6/95	
R		M09-0058		MHT		4/04/09		enrg		D. WHITING		6/6/95	
S		N10-0122		YO		5/10/10		chr		D. WHITING		6/6/95	
T		ELX-N-009749		YO		1/31/12		appd		D. WHITING		6/6/95	
sheet		revision		T		T		T		T		T	
index		sheet		1		2		3		4		5	




PRODUCT NUMBER
SEE TABLE

LOCATOR/HOLDDOWN VARIATIONS


STYLE
1





STYLE
2




STYLE
4





STYLE
6



STYLE
7




mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE				
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title				
T					angles	linear	.XX±.01/0.3		INCH/MM		RIBCAGE III T/M VERT. HEADER ASS'Y			
					.XXX±.005/0.13									
					0氣2? .XXXX±.0020/0.051									
					dr	M. CORNMAN	6/6/95		FCI 					dwg no
					engr	D. WHITING	6/6/95				95776		A3	
					chr	D. WHITING	6/6/95				type Product Customer Drawing			
					appd	D. WHITING	6/6/95							
sheet index		revision sheet												


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
6




STYLE
2



STYLE
7



STYLE
4




mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302 ✓	ISO 406 ISO 1101	ISO 406 ISO 1101	RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
T					angles	linear	RIBCAGE III T/M		
					0.002?		VERT. HEADER ASS'Y		
							dwg no		
					dr	M. CORNMAN	6/6/95	sheet 4 of 6	size
					enr	D. WHITING	6/6/95	95776	A3
					chr	D. WHITING	6/6/95	type	
					appd	D. WHITING	6/6/95	Product Customer Drawing	
sheet	revision								
index	sheet								


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
2



STYLE
4



STYLE
6



mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 	product family RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified				title		
T					angles	linear	.XX±.01/0.3	INCH/MM	RIBCAGE III T/M VERT. HEADER ASS'Y		
					0氣2?		.XXX±.005/0.13				
							.XXXX±.0020/0.051	scale 4:1	dwg no sheet 5 of 6 size		
					dr	M. CORNMAN	6/6/95		95776		
					enrg	D. WHITING	6/6/95		A3		
					chr	D. WHITING	6/6/95				
					appd	D. WHITING	6/6/95		type Product Customer Drawing		
sheet index	revision sheet										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[87407-120](#)