

4		3		2		1							
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS					
© COPYRIGHT — By —		ALL RIGHTS RESERVED.		—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
									A1	REVISED PER EC0-12-016312	13SEP12	KH	DR
INSULATION SLEEVE SERRATIONS BODY 0.78 [.031] MIN 7.12 [.280] MIN 20.0 [.772] MAX 1.0 [.040] 1 WIRE RANGE: 22-16AWG 2 INSULATION RANGE: 2.7-3.6 [.105-.140] DIA 3 TAB MATERIAL-THICKNESS 0.8[.033] MAX 4 MATERIAL: BODY&SLEEVE: COPPER PER ASTM B152 INSULATION: NYLON. 5 FINISH: TIN PLATE PER ASTM B545 INSULATION: COLOR-RED													
165446 PART NO													
CUSTOMER SERVICE SYSTEMS				MAX RECOMMENDED OPERATING TEMPERATURE: 105°[221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN HOLAL 13SEP2012		TE TE Connectivity			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300V MAX		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK ROHDE DANIEL 13SEP2012		NAME	
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 0.26-1.6 mm² SOLID OR STRANDED				0 PLC ± - 1 PLC ± 0.2[.008] 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD ROHDE DANIEL 13SEP2012		PRODUCT SPEC	
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL		FINISH		APPLICATION SPEC		SIZE	
						4		5		WEIGHT		A300779	
										CUSTOMER DRAWING		C-165446	
										SCALE 1:1		SHEET 1 OF 1	
										REV A1			