




PHYSICAL

Conductors: 28-7/38 AWG Tinned Copper
 Insulation: .010" Gray PVC
 Wrap: Polyester
 Temperature Rating: 105°C
 Jacket: .030" Nom Black PVC

ELECTRICAL

Impedance: 90 ohms
 Capacitance: 30 pF/ft @ 1 MHz
 Propagation Delay: 1.6 ns/ft
 Voltage Rating: 300 V
 Current Rating: 1 A at 10°C Rise Above Ambient
 Insul. Resistance: 10^{10} - 10 ft MIN.

Above values measured Ground-Signal-Ground

All Dimensions in Inches Unless Otherwise Noted

Approvals: UL CL2 105 C
 CSA AWM FT-1

Part Number	Count	A Span, Inches(mm)	B Span, Inches(mm)	C Span
151-2811-010	10	.500(12,70) Nom	.450±0.007(11,43±0,18)	.560
151-2811-014	14	.700(17,78) Nom	.650 ±0.007(16,51±0,18)	.760
151-2811-016	16	.800(20,32) Nom	.750 ±0.011(20,32±0,28)	.860
151-2811-020	20	1.000(25,40) Nom	.950 ±0.011(24,13±0,28)	1.060
151-2811-024	24	1.200(30,48) Nom	1.150 ±0.011(29,21±0,28)	1.260
151-2811-025	25	1.250(31,79) Nom	1.200 ±0.011(30,48±0,28)	1.310
151-2811-026	26	1.300(33,02) Nom	1.250 ±0.011(31,75±0,28)	1.360
151-2811-034	34	1.700(43,18) Nom	1.650 ±0.011(41,90±0,28)	1.760
151-2811-036	36	1.800(45,72) Nom	1.750 ±0.015(44,45±0,38)	1.860
151-2811-037	37	1.850(46,99) Nom	1.800 ±0.015(45,72±0,38)	1.910
151-2811-040	40	2.000(50,80) Nom	1.950 ±0.015(49,53±0,38)	2.060
151-2811-050	50	2.500(63,50) Nom	2.450 ±0.015(62,23±0,38)	2.560
151-2811-060	60	3.000(76,20) Nom	2.950 ±0.015(74,93±0,38)	3.060
151-2811-064	64	3.200(81,28) Nom	3.150 ±0.015(80,01±0,38)	3.260

DRAWN	PROD ENG	QA	MKT	P/ECN#	DRAWING NO.	151-2811-OXX		Rev	__
FTTS	06/26/98	06/30/98		201	TITLE:	Jacketed Planar Cable,		Sheet	1 of 1
						Zip Inner			

AMPHENOL SPECTRA-STRIP
 720 SHERMAN AVE TEL (203) 281-3200
 HAMDEN CT 06514 FAX (203) 281-5872