




MGPWC-00060-P	REV	 Tyco Electronics					
1879559-1	BA	CM Choke, RoHS TTI7570 Previously MGPWC-00060					
Product Description	CM Choke, RoHS TTI7570 Previously MGPWC-00060						
	  						
	<p>Terminal Dimensions Customer to determine PCB pad dimensions.</p> <p>Schematic</p> 						
<p>Primary Units are in inches millimetres in brackets</p> <p>Electrical Specifications at +20°C unless noted otherwise</p>							
Test	Limits	Unit	Tol	Notes			
Inductance	3.70	mH	±20%	2-1, 10kHz, 100mVAC, Ls.			
Inductance	3.70	mH	±20%	3-4, 10kHz, 100mVAC, Ls.			
Leakage Inductance	5.00	uH	Max.	1-2 Tie(3+4), 10kHz, 100mVAC,Ls.			
DC Resistance	1.5	Ω	Max.	Pins 1 - 2			
DC Resistance	1.5	Ω	Max.	Pins 3 - 4			
Dielectric	500	VDC		1-3, 1 second test			
<p>Terminal Plating is Gold Flash over Ni</p> <p>260°C Maximum reflow temperature per J-STD-020B</p> <p>Operating Temperature Range: -40°C to +85°C</p> <p>The information contained in this drawing is the sole property of Tyco Electronics. Any reproduction or use without the written permission of Tyco Electronics is prohibited.</p> <p>Specifications subject to change without notice. For latest revision visit http://www.tycoelectronics.com</p>							
							
Page 1 of 1 Date 03/03/09							