

2SD1260, 2SD1260A

Silicon NPN triple diffusion planar type darlington

For power amplification

Complementary to 2SB0937, 2SB0937A

■ Features

- High forward current transfer ratio h_{FE}
- High-speed switching
- N type package enabling direct soldering of the radiating fin to the printed circuit board, etc. of small electronic equipment.

■ Absolute Maximum Ratings $T_C = 25^\circ\text{C}$

Parameter	Symbol	Rating	Unit
Collector-base voltage (Emitter open)	V_{CBO}	60	V
		80	
Collector-emitter voltage (Base open)	V_{CEO}	60	V
		80	
Emitter-base voltage (Collector open)	V_{EBO}	5	V
Collector current	I_C	2	A
Peak collector current	I_{CP}	4	A
Collector power dissipation $T_a = 25^\circ\text{C}$	P_C	35	W
		1.3	
Junction temperature	T_j	150	$^\circ\text{C}$
Storage temperature	T_{stg}	-55 to +150	$^\circ\text{C}$


■ Electrical Characteristics $T_C = 25^\circ\text{C} \pm 3^\circ\text{C}$

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Collector-emitter voltage (Base open)	V_{CEO}	$I_C = 30 \text{ mA}, I_B = 0$	60			V
			80			
Base-emitter voltage	V_{BE}	$V_{CE} = 4 \text{ V}, I_C = 2 \text{ A}$			2.8	V
Collector-base cutoff current (Emitter open)	I_{CBO}	$V_{CB} = 60 \text{ V}, I_E = 0$			1	mA
		$V_{CB} = 80 \text{ V}, I_E = 0$			1	
Collector-emitter cutoff current (Base open)	I_{CEO}	$V_{CE} = 30 \text{ V}, I_B = 0$			2	mA
		$V_{CE} = 40 \text{ V}, I_B = 0$			2	
Emitter-base cutoff current (Collector open)	I_{EBO}	$V_{EB} = 5 \text{ V}, I_C = 0$			2	mA
Forward current transfer ratio	h_{FE1}	$V_{CE} = 4 \text{ V}, I_C = 1 \text{ A}$	1000			—
	h_{FE2}^*	$V_{CE} = 4 \text{ V}, I_C = 2 \text{ A}$	1000		10000	
Collector-emitter saturation voltage	$V_{CE(\text{sat})}$	$I_C = 2 \text{ A}, I_B = 8 \text{ mA}$			2.5	V
Transition frequency	f_T	$V_{CE} = 10 \text{ V}, I_C = 0.5 \text{ A}, f = 1 \text{ MHz}$			20	MHz
Turn-on time	t_{on}	$I_C = 2 \text{ A}$			0.5	μs
Strage time	t_{stg}	$I_{B1} = 8 \text{ mA}, I_{B2} = -8 \text{ mA}$			4.0	μs
		$V_{CC} = 50 \text{ V}$			1.0	μs

Note) 1. Measuring methods are based on JAPANESE INDUSTRIAL STANDARD JIS C 7030 measuring methods for transistors.


2. *: Rank classification









Rank	R	Q	P
h_{FE2}	1000 to 2500	2000 to 5000	4000 to 10000



Note) Self-supported type package is also prepared.

Internal Connection





Request for your special attention and precautions in using the technical information and semiconductors described in this material

- (1) An export permit needs to be obtained from the competent authorities of the Japanese Government if any of the products or technologies described in this material and controlled under the "Foreign Exchange and Foreign Trade Law" is to be exported or taken out of Japan.
- (2) The technical information described in this material is limited to showing representative characteristics and applied circuits examples of the products. It neither warrants non-infringement of intellectual property right or any other rights owned by our company or a third party, nor grants any license.
- (3) We are not liable for the infringement of rights owned by a third party arising out of the use of the product or technologies as described in this material.
- (4) The products described in this material are intended to be used for standard applications or general electronic equipment (such as office equipment, communications equipment, measuring instruments and household appliances).
Consult our sales staff in advance for information on the following applications:
 - Special applications (such as for airplanes, aerospace, automobiles, traffic control equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
 - Any applications other than the standard applications intended.
- (5) The products and product specifications described in this material are subject to change without notice for modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.
- (6) When designing your equipment, comply with the guaranteed values, in particular those of maximum rating, the range of operating power supply voltage, and heat radiation characteristics. Otherwise, we will not be liable for any defect which may arise later in your equipment.
Even when the products are used within the guaranteed values, take into the consideration of incidence of break down and failure mode, possible to occur to semiconductor products. Measures on the systems such as redundant design, arresting the spread of fire or preventing glitch are recommended in order to prevent physical injury, fire, social damages, for example, by using the products.
- (7) When using products for which damp-proof packing is required, observe the conditions (including shelf life and amount of time let standing of unsealed items) agreed upon when specification sheets are individually exchanged.
- (8) This material may be not reprinted or reproduced whether wholly or partially, without the prior written permission of Matsushita Electric Industrial Co., Ltd.