


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	T2	REVISED PER ECO-16-004223	21JUL2016	NK	MZ



- 1

1.27μm [.000050] MIN TIN-LEAD OVER
1.27μm [.000050] MIN NICKEL.
- 2


0.76μm [.000030] MIN GOLD IN LOCALIZED
PLATE AREA, 0.25μm [.000010] MIN
GOLD ON THE REMAINDER ALL OVER
1.27μm [.000050] MIN NICKEL.
- 3

2.54μm [.000100] MIN TIN-LEAD OVER
1.27μm [.000050] MIN NICKEL.
- 4

2.54μm [.000100] MIN TIN OVER
1.27μm [.000050] MIN NICKEL.
- 5

1.27μm [.000050] MIN TIN OVER
1.27μm [.000050] MIN NICKEL.

OBSOLETE	4	SMALL PACK	2	202236-8	
		STANDARD	2	202236-7	
		SMALL PACK	5	202236-6	
		STANDARD	5	202236-5	
	3	SMALL PACK	1	202236-4	
		SMALL PACK	2	202236-3	
		STANDARD	1	202236-2	
		STANDARD	2	202236-1	
	FINISH SOLDER TAB		PACKAGING TYPE	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 27SEP90	TE Connectivity				
		CHK J.McCLINTON 15DEC90					
DIMENSIONS: mm [INCHES]		APVD A. BOULLIANNE 15DEC90	NAME PIN ASSEMBLY, LOOSE PIECE, TYPE III+				
		PRODUCT SPEC —					
MATERIAL SEE CALL OUT		4 PLC ± — 3 PLC ± — 2 PLC ± 0.13[.005] 1 PLC ± — 0 PLC ± — ANGLES ± —	APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C=202236	RESTRICTED TO —
		FINISH PIN BODY:SEE TABLE	WEIGHT —				
CUSTOMER DRAWING			SCALE 8:1	SHEET 1 of 1	REV T2		