

10

9

8

7

6



5

4

3

2

19034



MATERIAL: COPPER
 .031" NOM. THICKNESS
 FINISH: ELECTRO-TIN PLATING

MWID= MAX. WIRE INSULATION DIA.

PART NUMBERS ARE FOR LOOSE PIECE TO ORDER PARTS ON TAPE ADD A "T" TO END OF PART NUMBER

MATERIAL NO.	ENGR NO.	WIRE RANGE AWG	DIAMETER "D"	MAX. "L"	±.01 "B"	MWID	MIN. I.D.				INSULATION
190340002	A-259X	22-18	.180	.950	.450	.145	.056				PVC
190340005	A-269X	22-18	.156	.890	.450	.145	.056				PVC
190340007	B-279X	16-14	.180	.950	.450	.175	.084				PVC
190340009	B-289X	16-14	.156	.890	.450	.175	.084				PVC

REMOVED TAPE PARTS

EC NO: 2005/04/27
 DRWN: SHADECK 2005/05/04
 CHKDR: DEROSS 2005/05/04
 APPR: DEROSS 2005/05/04

QUALITY
 SYMBOLS
 ▽=0
 ▽=0

GENERAL TOLERANCES
 (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±---	±---
3 PLACES	±---	±---
2 PLACES	±---	±---
1 PLACE	±---	±---
ANGULAR	±----	°

DRAFT WHERE APPLICABLE
 MUST REMAIN
 WITHIN DIMENSIONS

DIMENSION STYLE
 IN/MM

DRAWN BY	DATE
EMF	07/30/93
CHECKED BY	DATE
JM	07/30/93
APPROVED BY	DATE
FP	07/30/93

SCALE
 5:1

DESIGN UNITS
 INCH

THIRD ANGLE
 PROJECTION

INSULKRIMP
 MALE BULLET SNAP PLUG

MOLEX INCORPORATED

MATERIAL NO.
 SEE TABLE

DOCUMENT NO.
 SD-19034-004

SHEET NO.
 1 OF 1

9

8

7

6

5

4

3

2

1