

Detailed Specifications & Technical Data

BELDEN
SENDING ALL THE RIGHT SIGNALS

ENGLISH MEASUREMENT VERSION

83396 Multi-Conductor - Control and Instrumentation Cable



For more Information
please call

1-800-Belden1



Description:

22 AWG stranded (7x30) TC conductors, conductors cabled, 22 AWG (7x30) stranded TC drain wire, FEP insulation, special Beldfoil® shield (100% coverage), silicone rubber jacket, noise reducing tape.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
4	22	7x30	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (in.)
Teflon®	FEP - Fluorinated Ethylene Propylene	.015

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Tape	Noise Reducing Conductive Nylon	

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	7x30	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
Silicone Rubber	.030

Overall Cabling

Overall Cabling Lay Length & Direction:

Length (in.)	Twists (ft.)
1	12

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red
4	Green

Overall Nominal Diameter: 0.217 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +150°C

Bulk Cable Weight: 32 lbs/1000 ft.

Max. Recommended Pulling Tension: 40 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.250 in.

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

83396 Multi-Conductor - Control and Instrumentation Cable

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading, VW-1
----------------	-------------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
22

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
40

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
17.5

Max. Operating Voltage - UL:

Voltage	Description
2000 V DC	through jacket
350 V RMS	between conductors

Max. Recommended Current:

Current
2.8 Amps per conductor @ 25°C

Notes (Overall)

Notes (Cont'd.):	Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.
------------------	---

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
83396 002100	100 FT	3.900 LB	RED		4 #22 FEP FS SIL
83396 002500	500 FT	16.000 LB	RED	C	4 #22 FEP FS SIL

Notes:

C = CRATE REEL PUT-UP.

83396 Multi-Conductor - Control and Instrumentation Cable

Revision Number: 1 Revision Date: 09-18-2008

© 2011 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.