

TYPICAL INDICATOR ORDERING EXAMPLE

P01

12

C

1

A

Lamps

Incandescent

06	6-volt
12	12-volt
18	18-volt
24	24-volt
28	28-volt

Neon

N	110-volt
---	----------

Cap Colors

B	White
C	Red
D	Orange
E	Yellow
*F	Green
*G	Blue

*F & G not suitable with neon.

Bezels

1	.787" (20.0mm) Wide
2	.937" (23.8mm) Wide

Bezel Colors

A	Black
B	White
C	Red
D	Orange
E	Yellow
F	Green
G	Blue
H	Gray

DESCRIPTION FOR TYPICAL ORDERING EXAMPLE

P01-12-C-1A



Note: Wire harness & cable assemblies offered only in Americas

LAMP CODES & SPECIFICATIONS

Incandescent & Neon Lamps for Solid & Design Caps

AT602 Incandescent	AT602N Neon		06	12	18	24	28	N
								
T-1 ½ Pilot Slide Base								

Electrical specifications are determined at a basic temperature of 25°C.

For dimension drawings of lamps, see Accessories & Hardware Index.

If the source voltage is greater than rated voltage, a ballast resistor is required.

The ballast resistor calculation and more lamp detail are shown in the Supplement section.

CAP COLORS


B	White	D	Orange	F	Green
C	Red	E	Yellow	G	Blue

Material: Polycarbonate


Finish: Glossy

F & G not suitable for neon


AT429




OPTIONAL BEZELS & COLORS



AT204
.787" (20.0mm) Wide Bezel



AT9201
.937" (23.8mm) Wide Bezel







Material: Polycarbonate

Standard Finish: Glossy

Color Codes: A Black B White C Red D Orange E Yellow F Green G Blue H Gray

TYPICAL INDICATOR DIMENSIONS





Without Bezel



Panel Thickness:
 .039" ~ .157"
 (1.0mm ~ 4.0mm)

P01-12-C





With Bezel



Panel Thickness:
 .039" ~ .157"
 (1.0mm ~ 4.0mm)

P01-12-C-1A

With Large Bezel



Panel Thickness:
 .039" ~ .157"
 (1.0mm ~ 4.0mm)

P01-12-C-2A