

New Product

HIGH CURRENT POWER INDUCTOR SERIES SHCI1305

FEATURES

- RoHS compliant
- Ultra high power density
- Manufacturing friendly package
- High durability construction
- Perfect for use in video cards, motherboards and automotive computer applications

ELECTRICAL SPECIFICATIONS


- Inductance range 0.68uH to 2.7uH
- Test condition 0.1Vrms @ 100kHz
- Test equipment Quadtech 1750 LCR Meter

PHYSICAL SPECIFICATIONS

- Operating temp. -25°C to +125°C
- Core Alloy powder
- Packaging T & R 600 pieces per reel
- Tape & reel spec. Tape 24 mm embossed carrier
- Reel 330 mm dia


Dimensions in millimeters

Length A	12.7 ± 0.4
Width B	12.7 ± 0.4
Height C	5.3 ± 0.3
Terminal length D	2.0 ± 0.2
Term pitch E	7.0 ± 0.5



Suggested PCB land pattern

F	7.0
G	3.0
H	3.3



Notes:

1. Based on ΔL of 10% / 20% typical
2. Based on max ΔT of 45°C

All test data based on 25°C ambient. Part temperature (ambient+temp rise) must not exceed 125°C under worst case operating conditions.
Circuit design, components, PCB trace size and thickness, airflow and other cooling provisions all effect the part temperature.