



PART NUMBER TABLE

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM "A"	DIM "B"	DUAL END WALL OPTION
76055- *12*	10	50	21.7	17.10	
76055- *22*	12	60	25.5	20.90	
76055- *72*	14	70	29.3	24.70	
76055- *62*	16	80	33.1	28.50	




DUAL END
WALL OPTION

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM "A"	DIM "B"	LEFT END WALL OPTION
76055- *11*	10	50	20.3	17.10	
76055- *21*	12	60	24.1	20.90	
76055- *71*	14	70	27.9	24.70	
76055- *61*	16	80	31.7	28.50	




LEFT END
WALL OPTION

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM "A"	DIM "B"	RIGHT END WALL OPTION
76055- *13*	10	50	20.3	17.10	
76055- *23*	12	60	24.1	20.90	
76055- *73*	14	70	27.9	24.70	
76055- *63*	16	80	31.7	28.50	



RIGHT END
WALL OPTION

MATERIAL NUMBER	# OF COLUMNS	# OF DIFF PAIR	DIM "A"	DIM "B"	OPEN WALL OPTION
76055- *10*	10	50	18.9	17.10	
76055- *20*	12	60	22.7	20.90	
76055- *70*	14	70	26.5	24.70	
76055- *60*	16	80	30.3	28.50	



OPEN
WALL OPTION

SEE SHEET 1 EC NO: UCP2013-2078 DRWN: TIBARRA 2012/11/26 CHKD: JB INGHAM 2012/12/18 APPR: SMILLER 2012/12/31	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY JLAURX	DATE 2007/06/18	TITLE IMPACT 5 PAIR HEADER UNGUIDED ASSEMBLY SALES DRAWING molex			
			4 PLACES	± ---	± ---	CHECKED BY JLAURX	DATE 2007/06/18				
			3 PLACES	± ---	± ---	APPROVED BY	DATE				
			2 PLACES	± 0.13	± ---	JLAURX	2010/10/15				
			1 PLACE	± 0.25	± ---	MATERIAL NO.				DOCUMENT NO.	SHEET NO.
			0 PLACE	±	±	SEE TABLE				SD-76055-001	2 OF 3
			ANGULAR ±1/2°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

PART NUMBER LOGIC

76055-****




P=PIN LENGTH
3 = 4.50 (SHORT COMPLIANT, 0.46±0.05 PTH)
4 = 4.90 (SHORT COMPLIANT, 0.46±0.05 PTH)
5 = 5.50 (SHORT COMPLIANT, 0.46±0.05 PTH)
6 = 4.50 (MICRO COMPLIANT, 0.39±0.05 PTH)
7 = 4.90 (MICRO COMPLIANT, 0.39±0.05 PTH)
8 = 5.50 (MICRO COMPLIANT, 0.39±0.05 PTH)

MODULE TYPE
1 = UNGUIDED,TIN

OF COLUMNS
1 = 10 COL
2 = 12 COL
6 = 16 COL
7 = 14 COL

END WALL OPTIONS
0 = OPEN ENDS
1 = LEFT END WALL
2 = DUAL END WALL
3 = RIGHT END WALL

IMPACT 5 PAIR BOARD RELATIONSHIPS



SEE SHEET 1 EC NO: UCP2013-2078 DRWN:TIBARRA 2012/11/26 CHKD:JBINGHAM 2012/12/18 APPR:SMILLER 2012/12/31 J	REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	TITLE	DOCUMENT NO.	SHEET NO.			
					MM ONLY		2:1	METRIC					IMPACT 5 PAIR HEADER UNGUIDED ASSEMBLY SALES DRAWING molex SD-76055-001 3 OF 3		
					mm	INCH	DRAWN BY	DATE						JLAURX 2007/06/18	
					4 PLACES ± ---	± ---	CHECKED BY	DATE							
					3 PLACES ± ---	± ---	JLAURX	2007/06/18							
					2 PLACES ± 0.13	± ---	APPROVED BY	DATE							
					1 PLACE ± 0.25	± ---	JLAURX	2010/10/15						SEE TABLE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
					0 PLACE ±	±	MATERIAL NO.	SIZE							
					ANGULAR ±1/2°		C								
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										