




- 1 CONTINUOUS STRIP ON REELS.
- 2 REVERSE REELING.
- 3 FEED TO BE .440±.003.
- 4 PRELIMINARY – NOT FOR PRODUCTION.

SECTION X-X

SECTION Y-Y

	.000150 MIN SILVER/ BRASS			4 42490-6 2
	.000150 MIN NICKEL/ STEEL			4 42490-5
	—			2 42490-4
	TIN / BRASS	.080—.120 DIA	22-18 AWG	2 42490-3
OBSOLETE	TIN / BRASS			42490-2
OBSOLETE	—			42490-1
	FINISH / MATERIAL	INSULATION RANGE	WIRE SIZE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 1/31/91	STE TE Connectivity		
		CHK MS FEHER 1/31/91			
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C MEYERS 1/31/91	NAME		
	0 PLC ± —	PRODUCT SPEC	TAB, FASTON, .187 SERIES		
	1 PLC ± —	—			
	2 PLC ± —	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
	3 PLC ± .015	—			
MATERIAL	4 PLC ± —	WEIGHT —	A300779C-42490		
	ANGLES ± —				
SEE TABLE	FINISH	CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1	REV M
SEE TABLE					