

PART NO. ENG. NO.

02-06-2101	1560-(P901)
02-06-2103	1560-(P901)L
02-06-6101	1560-(561)
02-06-6102	1560-(561)L
02-06-6118	1560-(228)
02-06-6119	1560-(228)L
02-06-6116	1560-(231)
02-06-6112	1560-(231)L
02-06-6100	1560-(550)
02-06-6103	1560-(550)L
02-06-6105	1560-(591)
02-06-6104	1560-(591)L

LEGEND

1560-(****)*

P=PREPLATE
BLANK=POSTPLATE

FORM
BLANK=CHAIN
L=LOOSE

FINISH CODE

NOTES:

1. MATERIAL: BRASS

2. FINISHES:

901 HOT TIN DIP (.00051)/.000020 MIN.

*228 SELECT GOLD PLATE (.00075)/.000030 MIN. IN CONTACT AREA, SELECT TIN
(.00250)/.000100 MIN. IN CRIMP AREA OVER (.00125)/.000050 MIN. NICKEL OVERALL.

*231 SELECT GOLD PLATE (.00125)/.000050 MIN. IN CONTACT AREA, SELECT TIN
(.00250)/.000100 MIN. IN CRIMP AREA OVER (.00125)/.000050 MIN. NICKEL OVERALL.

561 SELECT GOLD PLATE (.00076)/.000030 MIN. IN CONTACT AREA, OVER
(.00127)/.000050 MIN. NICKEL OVERALL.

591 SELECT GOLD PLATE (.00127)/.000050 MIN. IN CONTACT AREA, OVER (.00127)/.000050
MIN. NICKEL OVERALL WITH (.000025)/.000010 MAX. GOLD FLASH OVERALL.


550 SELECT GOLD PLATE (.00038)/.000015 MIN. IN CONTACT AREA, OVER (.00076)/.000030
MIN. NICKEL OVERALL WITH (.000025)/.000010 MAX. GOLD FLASH OVERALL.

* THE PRIMARY SHIPPING CARTON WILL BE LABELED, 'COMPLIANT TO RoHS DIRECTIVE'
2002/95/EC AND ELV ANNEX II OF DIRECTIVE 2000/53/EC', AND CARTONS WITHOUT THIS
LABEL MAY CONTAIN PRODUCT WITH TIN-LEAD.

3. PRODUCT SPECIFICATION: PS-02-06

4. PACKAGING INFORMATION: NOT AVAILABLE

5. TERMINAL FOR USE WITH (.157)/.062 DIA. SERIES HOUSINGS AND
WILL ACCEPT 18 THRU 24 AWG WIRE.




SECT. "A-A"

SECT. "B-B"

SCALE:10X

SECT. "C-C"

SCALE:10X



CARRIER VIEW
ACTUAL SIZE

AP	REVSE Sn/Pb PLATE REDRAWN TO ME10 UCP2004-2097 RHOLTS 5/07/04
A0	REINSTATE 02066105 UCP2003-1827 ELHAG, 03/02/24
AN	OBSOLETE P/N UCR2002-0270 COMERC 01/9/25
AM1	ADDED ISO VIEW UCR1998-0228 WANG 98-05-21
AM	REV. & REDRAWN PER ECR 10372 GEP 8-19-87 RW

REFER TO REVISION BLOCK EC NO.: 2003/02/00/07097 DRAWN: RHOLTS 2004/05/14 CHKD: 2004/05/14 APPR: F SMITH 2004/05/18 REV	QUALITY SYMBOLS ▽ = 0 ◻ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE 8:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		REVISE ON CAD ONLY	
				DIMENSION STYLE IN/MM		TITLE			
		mm INCH		DRAWN BY DATE		CRIMP TERMINAL, MALE .062 DIA. FOR 18-24 AWG WIRE			
		4 PLACES ± --- ± ---		GEP 1987/08/19		MOLEX MOLEX INCORPORATED			
		3 PLACES ± --- ± .010		CHECKED BY DATE					
		2 PLACES ± 0.25 ± .014		RW 1987/08/19		MATERIAL NO.		DOCUMENT NO.	
		1 PLACE ± 0.35 ± ---		APPROVED BY DATE		SEE CHART		SD-1560-*	
		ANGULAR ±1/2°		RAS 1987/08/19		SHEET NO.		1 OF 1	
		DRAFT WHERE APPLICABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
		MUST REMAIN WITHIN DIMENSIONS							