

REVISIONS

ZONE	LTR	DESCRIPTION	DATE	APPROVED
	E	REDRAWN & REVISED 2078	4-15-9	M.S. L.H.
	F	OBSOLETE 66071-2 PER ECN 3341	2-4-72	J.W. D.H.
	G	PRINT DIST WAS "39" LOC WAS "AB" 9347	10-72	CO
	H	BRIGHT TIN-LEAD WAS TIN EA 1818	6-18-81	DS

SLEEVE MATL.-NYLON
COLOR - YELLOW $\pm .008$
.061 TAPER PER
INCH ON DIA. $\pm .0015$

.0560 DIA.

 $\pm .010$
.095 DIA. $\pm .010$

.290

.025

 $\pm .030$

.825

WIRE SIZE : #24 - #22
INS. RANGE : .040 - .080.080 - .090 DIA. TO A MIN.
DEPTH OF .090.

.145 DIA. REF.

TAPER PIN MATL.-
BRASS.033
MIN.
DIA..710
MAX. INSTALLED EXTENSION
(AFTER CRIMPING)

ASSY. BEFORE CRIMPING

66071-3 .000030 GOLD OVER .000050 NICKEL

~~66071-2 SILVER - .0002 THICK~~

66071-1 BRIGHT TIN-LEAD .0002 THICK

PART NO.

FINISH

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES
TOLERANCES ON:
DECIMALS $\pm .015$
ANGLES $\pm \#$

MATERIAL

SEE
CALLOUT

CONTRACT NO.

DR. *M. Smith* 4-15-69CHK. *L.S. Heide* 5-12-69APPD. *C. Snyder* 5/15/69REL. *W. Felt* 5-15-69

DSGN APPD.

OTHER APPD.

AMP

AMP INCORPORATED
HARRISBURG, PENNSYLVANIANAME
PIN, TAPER,
53" SERIES, P.I.D.G..

SIZE

B

CODE IDENT NO.

00779

NUMBER

66071

SCALE

#

SHEET

CUSTOMER DRAWING