

NLSF2500

Keypad Multiplexer

The NLSF2500 is a keyboard multiplexer fabricated in sub-micron silicon CMOS Technology. The NLSF2500 is designed to operate over wide operating voltage, with minimum power consumption and very low voltage drop from V_{CC}. The device saves dozens of active and passive components and permits operating voltage far lower than the standard diode scheme.

Features

- Single Supply Operation
- Optimized for 1.8 V to 3.6 V V_{CC}
- Tiny 3 x 3 mm QFN-16 Package
- Conforms to: JEDEC MO-220, Issue H, Variation VEED-6
- Very Low Voltage Drop
- Permits Operation Down to 1.65 V
- Near Zero Static Power
- ESD Protection: Human Body Model (HBM); > 3000 V, Machine Model (MM); > 300 V
- Latchup Maximum Rating: 200 mA
- Pin-to-Pin Compatible with CM2500
- This is a Pb-Free Device

Typical Applications


- Cell Phones
- PDAs
- MP3 players



ON Semiconductor®

<http://onsemi.com>


MARKING DIAGRAM



QFN-16
CASE 485AE

XXXX = Specific Device Code
A = Assembly Location
L = Wafer Lot
Y = Year
W = Work Week
▪ = Pb-Free Package

PIN CONNECTIONS



ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 4 of this data sheet.

NLSF2500




Figure 1. Device Block Diagram




Figure 2. Circuit Schematic (1 Channel Pair Only)

PIN DESCRIPTION

Pin	Name	Function Description
1	NC	Not Internally Connected
2	OUTA	Combined "Functional OR" Output of IN1, IN2, and IN3
3	V _{CC}	Supply Pin
4	IN1	Input 1 from Switch to be Multiplexed
5	IN2	Input 2 from Switch to be Multiplexed
6	IN3	Input 3 from Switch to be Multiplexed
7	IN4	Input 4 from Switch to be Multiplexed
8	IN5	Input 5 from Switch to be Multiplexed
9	NC	Not Internally Connected
10	GND	Ground
11	OUTB	Combined "Functional OR" Output of IN4 and IN5
12	OUT5	Output 5 for Keyboard Interface Lines
13	OUT4	Output 4 for Keyboard Interface Lines
14	OUT3	Output 3 for Keyboard Interface Lines
15	OUT2	Output 2 for Keyboard Interface Lines
16	OUT1	Output 1 for Keyboard Interface Lines

MAXIMUM RATINGS

Symbol	Rating	Value	Unit
V_{CC}	DC Supply Voltage	-0.5 to +7.0	V
V_I	DC Input Voltage	$0 \leq V_{CC} \leq V_{CC} + 0.5$	V
V_O	DC Output Voltage	- 0.5 to + 7.0	V
I_{IK}	DC Input Diode Current $V_I < GND$	± 50	mA
I_{OK}	DC Output Diode Current $V_O = GND$	- 50	mA
I_O	DC Output Sink Current	± 50	mA
I_{CC}	DC Supply Current per Supply Pin	± 100	mA
I_{GND}	DC Ground Current per Ground Pin	± 100	mA
T_{STG}	Storage Temperature Range	- 65 to + 150	°C
T_L	Lead Temperature, 1 mm from Case for 10 Seconds	260	°C
T_J	Junction Temperature under bias	+ 150	°C
θ_{JA}	Thermal Resistance	80	°C/W
P_D	Power Dissipation in Still Air at 85°C	800	mW
MSL	Moisture Sensitivity	Level 1	
F_R	Flammability Rating Oxygen Index: 28 to 34	UL 94 V-0 @ 0125 in	
V_{ESD}	ESD Test Voltage Human Body Model (Note 1) Machine Model (Note 2)	> 3000 > 300	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Tested to EIA/JESD22-A114-A.
2. Tested to EIA/JESD22-A115-A.

RECOMMENDED OPERATING CONDITIONS

Symbol	Characteristics	Min	Max	Unit
V_{CC}	Positive DC Supply Voltage	1.5	5.5	V
V_{IN}	DC Input Voltage	GND	$V_{CC} + 0.5$	V
V_{OUT}	DC Output Voltage	GND	5.5	V
T_A	Operating Temperature Range	40	85	°C

DC CHARACTERISTICS

Symbol	Parameter	Condition	V_{CC}	Min	Max	Unit
V_{IL}	Input Logic Low Voltage		1.65 – 3.6	$0.3 * V_{CC}$		V
V_{IH}	Input Logic High Voltage		1.65 – 3.6		$0.7 * V_{CC}$	V
R_{OUT}	OUT_x Pullup Resistance		1.65 – 3.6	50	150	kΩ
$R_{IN\ 2.7}$	IN_x Pullup Resistance	$PIN = GND$	2.7	50	150	kΩ
$R_{IN\ 1.8}$	IN_x Pullup Resistance	$PIN = GND$	1.8	100	360	kΩ
V_D	Voltage Drop	$IN_x = GND, I_{OUT} = 100\ \mu A$			100	mV
I_{CC}	Quiescent Current	All I/O Floating	1.65 – 3.6		10	μA
I_L	Output Leakage Current	$IN_x = Floating$			1.0	μA
C_P	I/O Pin Capacitance	1.0 MHz	2.5		15	pF

ORDERING INFORMATION


Device Order Number	Device Nomenclature					Package Type	Tape & Reel Size [†]
	Circuit Indicator	Technology	Device Function	Package Suffix	Tape and Reel Suffix		
NLSF2500MN1R2G	NL	SF	2500	MN1	R2	QFN-16 (Pb-Free)	3000

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

OBSOLETE
PLEASE CONTACT YOUR ON SEMICONDUCTOR
REPRESENTATIVE FOR INFORMATION

PACKAGE DIMENSIONS

QFN-16 3*3*0.85 MM, 0.5 P
CASE 485AE-01
ISSUE O



NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION *b* APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.25 AND 0.30 MM FROM TERMINAL.
4. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.
5. OUTLINE MEETS JEDEC DIMENSIONS PER MO-220, VARIATION VEED-6.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	0.800	0.900	1.000
A1	0.000	0.025	0.050
A3	0.200	REF	
b	0.180	0.250	0.300
D	3.00	BSC	
D2	1.250	1.40	1.550
E	3.00	BSC	
E2	1.250	1.40	1.550
e	0.500	BSC	
K	0.200	---	---
L	0.300	0.400	0.500

ON Semiconductor and **ON** are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
 P.O. Box 5163, Denver, Colorado 80217 USA
 Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
 Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
 Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

USA/Canada

Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910

Japan Customer Focus Center

Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.comOrder Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ON Semiconductor](#):

[NLSF2500MN1R2G](#)