

# Autotransformer **AT3 10-38/42-4**



Picture shows AT3 2-20/21-4


## Advantages

- Low weight and small size (compared to isolating transformers)
- Very high efficiency
- Inverse operation possible
- Patented assembly technology to lower heat losses
- Very good corrosion protection and low noise thanks to BLOCKIMPEX vacuum impregnation
- Fixed, contact protected screw connection terminals complying with UVV BGV A3
- Multifunctional fixing rails with 12 oval slots
- Enlarged fixing rail for easy installation from above
- Integrated crane eyes

## Applications

Autotransformer for adjustment of the voltage on the input and output sides with no requirement for electrical isolation.

## Sample application



## Standards

Autotransformer  
to: VDE 0570 Teil 2-13, DIN EN 61558-2-13, EN 61558-2-13,  
IEC 61558-2-13, UL 5085-1/-2, CSA 22.2 No.66

## Approvals



UL 5085-1/-2, CSA 22.2 No.66



## Autotransformer **AT3 10-38/42-4**

### Electrical data

Type	AT3 10-38/42-4
Input	
Rated input voltage	3 x 380/415 Vac
Rated frequency	50 - 60 Hz
Output	
Rated output voltage	3 x 400 Vac
Rated Power	10000 VA
Vector group	YN <sub>a</sub> O
Efficiency	84 %
Approvals	
Approvals	cURus
Environment	
Ambient temperature max.	40 °C
Safety and protection	
Type	open type
Class of Insulation System	F
Protection index	IP 00
Safety class (prepared)	I
Short circuit strength	non-short-circuit proof
Test voltage	4000 Vac, 50 Hz
Order numbers	
Order Number	AT3 10-38/42-4

30

### Mechanical data

Type	AT3 10-38/42-4
Terminal and mounting	
Fixing method	Fixing rail
Fixing screws	M6
Terminals	Screw-type terminals
Measures and weights	
Weight	7.00 kg
Core type	3 UI 90/31,5

