








23.00
[0.906]CIRCUIT: 2P; SPST
CONTACT CONFIGURATION
ON-OFF (ILLUMINATED)ALIGNMENT
KEYWAY2.20 +0.1/-0.0
RECOMMEND PANEL MOUNTING

LED LEAD DETAIL

ALIGNMENT
KEY

SWITCH FUNCTION	
POS. 1	POS. 2
ON	OFF
2-1	OPEN

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 16A, 125VAC, 10A, 250VAC UL&CUL APPROVED
10A 125VAC, 6A 250V AC VDE APPROVED
5. CONTACT RESISTANCE: 50m ohm max.
6. INSULATION RESISTANCE: DC 500V 100M ohm min.
7. DIELECTRIC STRENGTHS: AC 1500V 1 minute
8. OPERATING TEMP.: 0°C to 85°C
9. 3V RED LED
10. ▲ DENOTES CRITICAL PARAMETER.

B	13813	UPDATE PART AND NOTES	3/2/04	AR
A	13317	RELEASED FOR PRODUCTION	7/25/03	AR
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE

RR3112LBLKBLKREDEF3

SCALE

2:1

DATE

7/25/03

DR

AR

DWG

F130452

REV

B