

Customer Information Sheet

DRAWING No.: M30-110XX00

SHEET 2 OF 2



IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



No. 1 POSITION

THIS FEATURE IS ON 05,
10 AND 15 SIZES ONLY.

SPECIFICATIONS:

MATERIAL:

MOULDING = NYLON 66 NATURAL, UL94V-0

ELECTRICAL:

CURRENT RATING = 1A AC/DC

VOLTAGE RATING = 150V AC/DC

CONTACT RESISTANCE = 30mΩ MAX

INSULATION RESISTANCE = 500MΩ MIN

DIELECTRIC WITHSTANDING VOLTAGE = 500V AC FOR ONE MINUTE

ENVIRONMENTAL:


TEMPERATURE RANGE = -25° TO +85°C

PACKING: BAG

FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION
C025XX (LATEST ISSUE)

NOTES:

1. TO BE USED IN CONJUNCTION WITH M30-1050046 OR M30-1060046 CRIMP CONTACTS. THE SPECIFICATIONS LISTED ARE APPROPRIATE WHEN USED WITH THESE CONTACTS.
2. MATES WITH M30-600XX46 AND M30-610XX46 PIN HEADERS.
3. ALL TOLERANCES ± 0.25 UNLESS OTHERWISE STATED.



ORDER CODE:

M30-110XX00

No. OF CONTACTS
02 TO 15

SB	9	01.07.13	12134
NAME	ISS.	DATE	C/NOTE
APPROVED:		S.BENNETT	
CHECKED:		M.PLESTED	
DRAWN:		D. BECK	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X = $\pm 1\text{mm}$
X.X = $\pm 0.25\text{mm}$
X.XX = $\pm 0.10\text{mm}$
X.XXX = $\pm 0.01\text{mm}$

ANGLES = $\pm 5^\circ$

UNLESS STATED

MATERIAL:

NYLON 66 UL94V-0
NATURAL

FINISH: CLEAN

S/AREA:

mm²

TITLE:

1.25mm PITCH SIL
CRIMP MOULDING

DRAWING NUMBER:

M30-110XX00

SHT
2
OF
2