

Universal Computer Power Cord, 10A, 18AWG (NEMA 5-15P to IEC-320-C13), 20-ft.

MODEL NUMBER: **P006-020**



Highlights

- Plug Type - NEMA 5-15P (AC) to IEC-320-C13 (Device)
- 18AWG, SJT, 10A, 125V
- UL Listed

Package Includes

- 20-ft. Universal AC Power Cord
 - NEMA 5-15P Plug to IEC-320-C13 Receptacle

Description

Tripp Lite's line of AC power cords offer PC users a solution to their power connectivity problems. This 20ft cable will replace the power cord on most computers and peripherals. Cable features an AC style plug (NEMA 5-15P) on one end and a computer style receptacle (IEC-320-C13) on the other end. UL Listed.

Features

- 20-ft. replacement power cable for a PC, printer, monitor or any other device with like plugs
- Universal design
- Plug type - NEMA 5-15P (AC) to IEC-320-C13 (Device)
- 18AWG, SJT, 10A, 125V
- UL Listed

Specifications

INPUT	
Cable Length (ft.)	20
Cable Length (m)	6.1
PHYSICAL	
Shipping Dimensions (hwd / in.)	1.000 x 11.000 x 15.000
Shipping Dimensions (hwd / cm)	2.54 x 27.94 x 38.10
Shipping Weight (lbs.)	1.4000



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (kg)	0.64
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Operating Humidity Range	10 - 85% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>