


# 74ACT11651 OCTAL BUS TRANSCEIVER AND REGISTER WITH 3-STATE OUTPUTS

SCAS134 – D3445, MARCH 1990 – REVISED APRIL 1993

- Inputs Are TTL-Voltage Compatible
- Bus Transceivers/Registers
- Independent Registers and Enables for A and B Buses
- Multiplexed Real-Time and Stored Data
- Inverting Data Paths
- Flow-Through Architecture to Optimize PCB Layout
- Center-Pin  $V_{CC}$  and GND Configurations to Minimize High-Speed Switching Noise
- EPIC™ (Enhanced-Performance Implanted CMOS) 1- $\mu$ m Process
- 500-mA Typical Latch-Up Immunity at 125°C
- Package Options Include Plastic Small Outline Packages and Standard Plastic 300-mil DIPs

DW OR NT PACKAGE  
(TOP VIEW)



## description

These devices consist of bus transceiver circuits, D-type flip-flops, and control circuitry arranged for multiplexed transmission of data directly from the data bus or from the internal storage registers. Enables  $\overline{GAB}$  and  $\overline{GBA}$  are provided to control the transceiver functions. SAB and SBA control pins are provided to select whether real-time or stored data is transferred. The circuitry used for select control eliminates the typical decoding glitch that occurs in a multiplexer during the transition between stored and real-time data.

A low input level selects real-time data and a high selects stored data. Figure 1 illustrates the four fundamental bus-management functions that can be performed with the octal bus transceivers and registers. Data on the A or B bus, or both, can be stored in the internal D flip-flops by low-to-high transitions at the appropriate clock pins (CAB or CBA) regardless of the select or enable control pins. When SAB and SBA are in the real-time transfer mode, it is also possible to store data without using the internal D-type flip-flops by simultaneously enabling  $\overline{GAB}$  and  $\overline{GBA}$ . In this configuration, each output reinforces its input. Thus, when all other data sources to the two sets of bus lines are at high impedance, each set of bus lines remains at its last state.

The 74ACT11651 is characterized for operation from – 40°C to 85°C.

EPIC is a trademark of Texas Instruments Incorporated.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

Copyright © 1993, Texas Instruments Incorporated

# 74ACT11651

## OCTAL BUS TRANSCEIVER AND REGISTER WITH 3-STATE OUTPUTS

SCAS134 – D3445, MARCH 1990 – REVISED APRIL 1993




Figure 1. Bus Transfer Diagram

**74ACT11651**  
**OCTAL BUS TRANSCEIVER AND REGISTER**  
**WITH 3-STATE OUTPUTS**

SCAS134 – D3445, MARCH 1990 – REVISED APRIL 1993


**FUNCTION TABLE**

| INPUTS |     |        |        |                |                | DATA I/O                 |                          | OPERATION OR FUNCTION                                                          |
|--------|-----|--------|--------|----------------|----------------|--------------------------|--------------------------|--------------------------------------------------------------------------------|
| GAB    | GBA | CAB    | CBA    | SAB            | SBA            | A1 THRU A8               | B1 THRU B8               |                                                                                |
| L      | H   | H or L | H or L | X              | X              | Input                    | Input                    | Isolation                                                                      |
| L      | H   | ↑      | ↑      | X              | X              | Input                    | Input                    | Store A and B Data                                                             |
| X      | H   | ↑      | H or L | X              | X              | Input                    | Unspecified <sup>†</sup> | Store A, Hold B                                                                |
| H      | H   | ↑      | ↑      | X <sup>‡</sup> | X              | Input                    | Output                   | Store A in both registers                                                      |
| L      | X   | H or L | ↑      | X              | X              | Unspecified <sup>†</sup> | Input                    | Hold A, Store B                                                                |
| L      | L   | ↑      | ↑      | X              | X <sup>‡</sup> | Output                   | Input                    | Store B in both registers                                                      |
| L      | L   | X      | X      | X              | L              | Output                   | Input                    | Real-Time $\overline{B}$ Data to A Bus                                         |
| L      | L   | X      | H or L | X              | H              | Output                   | Input                    | Stored $\overline{B}$ Data to A Bus                                            |
| H      | H   | X      | X      | L              | X              | Input                    | Output                   | Real-Time $\overline{A}$ Data to B Bus                                         |
| H      | H   | H or L | X      | H              | X              | Input                    | Output                   | Stored $\overline{A}$ Data to B Bus                                            |
| H      | L   | H or L | H or L | H              | H              | Output                   | Output                   | Stored $\overline{A}$ Data to B Bus and<br>Stored $\overline{B}$ Data to A Bus |

<sup>†</sup> The data output functions may be enabled or disabled by various signals at the GAB or  $\overline{GBA}$  inputs. Data input functions are always enabled, i.e., data at the bus pins will be stored on every low-to-high transition on the clock inputs.

<sup>‡</sup> Select control = L: clocks can occur simultaneously. Select control = H: clocks must be staggered in order to load both registers.

### logic symbols<sup>§</sup>



<sup>§</sup> This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

## SCAS134 – D3445, MARCH 1990 – REVISED APRIL 1993

7 Channels Identical To Channel 1 Above

|                                                                |                             |
|----------------------------------------------------------------|-----------------------------|
| Supply voltage range, $V_{CC}$                                 | −0.5 V to 7 V               |
| Input voltage range, $V_I$ (see Note 1)                        | − 0.5 V to $V_{CC} + 0.5$ V |
| Output voltage range, $V_O$ (see Note 1)                       | − 0.5 V to $V_{CC} + 0.5$ V |
| Input clamp current, $I_{IK}$ ( $V_I < 0$ or $V_I > V_{CC}$ )  | ± 20 mA                     |
| Output clamp current, $I_{OK}$ ( $V_O < 0$ or $V_O > V_{CC}$ ) | ± 50 mA                     |
| Continuous output current, $I_O$ ( $V_O = 0$ to $V_{CC}$ )     | ± 50 mA                     |
| Continuous current through $V_{CC}$ or GND                     | ± 200 mA                    |
| Storage temperature range                                      | − 65°C to 150°C             |

NOTE 1: The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

**74ACT11651**  
**OCTAL BUS TRANSCEIVER AND REGISTER**  
**WITH 3-STATE OUTPUTS**

SCAS134 – D3445, MARCH 1990 – REVISED APRIL 1993

**recommended operating conditions**

|                     |                                    | MIN | NOM      | MAX | UNIT |
|---------------------|------------------------------------|-----|----------|-----|------|
| $V_{CC}$            | Supply voltage                     | 4.5 | 5        | 5.5 | V    |
| $V_{IH}$            | High-level input voltage           | 2   |          |     | V    |
| $V_{IL}$            | Low-level input voltage            |     |          | 0.8 | V    |
| $V_I$               | Input voltage                      | 0   | $V_{CC}$ |     | V    |
| $V_O$               | Output voltage                     | 0   | $V_{CC}$ |     | V    |
| $I_{OH}$            | High-level output current          |     |          | -24 | mA   |
| $I_{OL}$            | Low-level output current           |     |          | 24  | mA   |
| $\Delta t/\Delta v$ | Input transition rise or fall rate | 0   |          | 10  | ns/V |
| $T_A$               | Operating free-air temperature     | -40 |          | 85  | °C   |

**electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)**

| PARAMETER                     |                           | TEST CONDITIONS                                             | V <sub>CC</sub> | T <sub>A</sub> = 25°C |     |     | MIN  | MAX | UNIT |
|-------------------------------|---------------------------|-------------------------------------------------------------|-----------------|-----------------------|-----|-----|------|-----|------|
|                               |                           |                                                             |                 | MIN                   | TYP | MAX |      |     |      |
| V <sub>OH</sub>               |                           | I <sub>OH</sub> = − 50 μA                                   | 4.5 V           | 4.4                   |     |     | 4.4  |     | V    |
|                               |                           |                                                             | 5.5 V           | 5.4                   |     |     | 5.4  |     |      |
|                               |                           | I <sub>OH</sub> = − 24 mA                                   | 4.5 V           | 3.94                  |     |     | 3.8  |     |      |
|                               |                           |                                                             | 5.5 V           | 4.94                  |     |     | 4.8  |     |      |
|                               |                           | I <sub>OH</sub> = − 75 mA <sup>†</sup>                      | 5.5 V           |                       |     |     | 3.85 |     |      |
| V <sub>OL</sub>               |                           | I <sub>OL</sub> = 50 μA                                     | 4.5 V           | 0.1                   |     |     | 0.1  |     | V    |
|                               |                           |                                                             | 5.5 V           | 0.1                   |     |     | 0.1  |     |      |
|                               |                           | I <sub>OL</sub> = 24 mA                                     | 4.5 V           | 0.36                  |     |     | 0.44 |     |      |
|                               |                           |                                                             | 5.5 V           | 0.36                  |     |     | 0.44 |     |      |
|                               |                           | I <sub>OL</sub> = 75 mA <sup>†</sup>                        | 5.5 V           |                       |     |     | 1.65 |     |      |
| I <sub>OZ</sub>               | A or B ports <sup>§</sup> | V <sub>I</sub> = V <sub>CC</sub> or GND                     | 5.5 V           | ± 0.5                 |     |     | ± 5  |     | μA   |
| I <sub>I</sub>                | Control Inputs            | V <sub>I</sub> = V <sub>CC</sub> or GND                     | 5.5 V           | ± 0.1                 |     |     | ± 1  |     | μA   |
| I <sub>CC</sub>               |                           | V <sub>I</sub> = V <sub>CC</sub> or GND, I <sub>O</sub> = 0 | 5.5 V           | 8                     |     |     | 80   |     | μA   |
| ΔI <sub>CC</sub> <sup>‡</sup> |                           | V <sub>I</sub> = V <sub>CC</sub> or GND                     | 5.5 V           | 0.9                   |     |     | 1    |     | mA   |
| C <sub>i</sub>                | Control Inputs            | V <sub>I</sub> = V <sub>CC</sub> or GND                     | 5 V             | 4.5                   |     |     |      |     | pF   |
| C <sub>io</sub>               | A or B ports              | V <sub>I</sub> = V <sub>CC</sub> or GND                     | 5 V             | 10                    |     |     |      |     | pF   |

<sup>†</sup> Not more than one output should be tested at a time, and the duration of the test should not exceed 10 ms.

<sup>‡</sup> This is the increase in supply current for each input that is at one of the specified TTL voltage levels rather than 0 V or  $V_{CC}$ .

<sup>§</sup> For I/O ports, the parameter  $I_{OZ}$  includes the input leakage current.

**timing requirements over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see Figure 2)**

|                    |                                                                | $T_A = 25^\circ\text{C}$ |     | MIN | MAX | UNIT |
|--------------------|----------------------------------------------------------------|--------------------------|-----|-----|-----|------|
|                    |                                                                | MIN                      | MAX |     |     |      |
| $f_{\text{clock}}$ | Clock frequency                                                | 0                        | 90  | 0   | 100 | MHz  |
| $t_w$              | Pulse duration, CAB or CBA high or low                         | 5.5                      |     | 5   |     | ns   |
| $t_{su}$           | Setup time, A before CAB $\uparrow$ or B before CBA $\uparrow$ | 4.5                      |     | 4.5 |     | ns   |
| $t_h$              | Hold time, A after CAB $\uparrow$ or B after CBA $\uparrow$    | 2                        |     | 0   |     | ns   |



# 74ACT11651

## OCTAL BUS TRANSCEIVER AND REGISTER WITH 3-STATE OUTPUTS

SCAS134 – D3445, MARCH 1990 – REVISED APRIL 1993

switching characteristics over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see Figure 2)

| PARAMETER        | FROM<br>(INPUT)                             | TO<br>(OUTPUT) | T <sub>A</sub> = 25°C |     |      | MIN | MAX  | UNIT |
|------------------|---------------------------------------------|----------------|-----------------------|-----|------|-----|------|------|
|                  |                                             |                | MIN                   | TYP | MAX  |     |      |      |
| f <sub>max</sub> |                                             |                | 90                    |     |      | 90  |      | MHz  |
| t <sub>PLH</sub> | A or B                                      | B or A         | 2.6                   | 5.6 | 8.9  | 2.6 | 9.9  | ns   |
| t <sub>PHL</sub> |                                             |                | 4.7                   | 7.7 | 10.7 | 4.7 | 11.9 |      |
| t <sub>PLH</sub> | CBA or CAB                                  | A or B         | 5.5                   | 8.4 | 11.2 | 5.5 | 12.7 | ns   |
| t <sub>PHL</sub> |                                             |                | 6.3                   | 9.5 | 12.7 | 6.3 | 14.1 |      |
| t <sub>PLH</sub> | SBA or SAB <sup>†</sup><br>with A or B high | A or B         | 4.8                   | 7.6 | 10.4 | 4.8 | 11.8 | ns   |
| t <sub>PHL</sub> |                                             |                | 4.1                   | 7.7 | 11.2 | 4.1 | 12.4 |      |
| t <sub>PLH</sub> | SBA or SAB <sup>†</sup><br>with A or B low  | A or B         | 3                     | 6.2 | 9.3  | 3   | 10.4 | ns   |
| t <sub>PHL</sub> |                                             |                | 5.6                   | 8.7 | 11.7 | 5.6 | 13   |      |
| t <sub>PZH</sub> | $\overline{\text{G}}\text{BA}$              | A              | 4                     | 7.4 | 10.7 | 4   | 11.9 | ns   |
| t <sub>PZL</sub> |                                             |                | 4.3                   | 8.2 | 11.9 | 4.3 | 13.3 |      |
| t <sub>PHZ</sub> | $\overline{\text{G}}\text{BA}$              | A              | 5.9                   | 7.7 | 9.5  | 5.9 | 10   | ns   |
| t <sub>PLZ</sub> |                                             |                | 5.1                   | 6.9 | 8.7  | 5.1 | 9.2  |      |
| t <sub>PZH</sub> | GAB                                         | B              | 5.9                   | 9   | 12.1 | 5.9 | 13.7 | ns   |
| t <sub>PZL</sub> |                                             |                | 6.4                   | 9.8 | 13.2 | 6.4 | 14.9 |      |
| t <sub>PHZ</sub> | GAB                                         | B              | 4.7                   | 7.1 | 9.5  | 4.7 | 10   | ns   |
| t <sub>PLZ</sub> |                                             |                | 3.8                   | 6.1 | 8.4  | 3.8 | 8.8  |      |

<sup>†</sup> These parameters are measured with the internal output state of the storage register opposite to that of the bus input.


operating characteristics, V<sub>CC</sub> = 5 V, T<sub>A</sub> = 25°C

| PARAMETER       |                                        | TEST CONDITIONS                   | TYP | UNIT |
|-----------------|----------------------------------------|-----------------------------------|-----|------|
| C <sub>pd</sub> | Power dissipation capacitance per gate |                                   | 61  | pF   |
|                 | Outputs disabled                       | C <sub>L</sub> = 50 pF, f = 1 MHz | 15  |      |

# 74ACT11651 OCTAL BUS TRANSCEIVER AND REGISTER WITH 3-STATE OUTPUTS

SCAS134 – D3445, MARCH 1990 – REVISED APRIL 1993

## PARAMETER MEASUREMENT INFORMATION



NOTES: A.  $C_L$  includes probe and jig capacitance.

B. All input pulses are supplied by generators having the following characteristics:  $PRR \leq 10 \text{ MHz}$ ,  $Z_O = 50 \Omega$ ,  $t_r \leq 3 \text{ ns}$ ,  $t_f \leq 3 \text{ ns}$ . For testing pulse duration:  $t_r = t_f = 1 \text{ to } 3 \text{ ns}$ . Pulse polarity can be either high-to-low-to-high or low-to-high-to-low.

C. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.

D. The outputs are measured one at a time with one transition per measurement.

Figure 2. Load Circuit and Voltage Waveforms

## PACKAGING INFORMATION

| Orderable Device | Status <sup>(1)</sup> | Package Type | Package Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup> | Lead/Ball Finish | MSL Peak Temp <sup>(3)</sup> |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|------------------------------|
| 74ACT11651DW     | OBSOLETE              | SOIC         | DW              | 28   |             | TBD                     | Call TI          | Call TI                      |
| 74ACT11651NT     | OBSOLETE              | PDIP         | NT              | 28   |             | TBD                     | Call TI          | Call TI                      |
| 74ACT11651NT     | OBSOLETE              | PDIP         | NT              | 28   |             | TBD                     | Call TI          | Call TI                      |

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS) or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

|                             |                                                                    |
|-----------------------------|--------------------------------------------------------------------|
| Amplifiers                  | <a href="http://amplifier.ti.com">amplifier.ti.com</a>             |
| Data Converters             | <a href="http://dataconverter.ti.com">dataconverter.ti.com</a>     |
| DLP® Products               | <a href="http://www.dlp.com">www.dlp.com</a>                       |
| DSP                         | <a href="http://dsp.ti.com">dsp.ti.com</a>                         |
| Clocks and Timers           | <a href="http://www.ti.com/clocks">www.ti.com/clocks</a>           |
| Interface                   | <a href="http://interface.ti.com">interface.ti.com</a>             |
| Logic                       | <a href="http://logic.ti.com">logic.ti.com</a>                     |
| Power Mgmt                  | <a href="http://power.ti.com">power.ti.com</a>                     |
| Microcontrollers            | <a href="http://microcontroller.ti.com">microcontroller.ti.com</a> |
| RFID                        | <a href="http://www.ti-rfid.com">www.ti-rfid.com</a>               |
| RF/IF and ZigBee® Solutions | <a href="http://www.ti.com/lprf">www.ti.com/lprf</a>               |

### Applications

|                            |                                                                                          |
|----------------------------|------------------------------------------------------------------------------------------|
| Audio                      | <a href="http://www.ti.com/audio">www.ti.com/audio</a>                                   |
| Automotive                 | <a href="http://www.ti.com/automotive">www.ti.com/automotive</a>                         |
| Communications and Telecom | <a href="http://www.ti.com/communications">www.ti.com/communications</a>                 |
| Computers and Peripherals  | <a href="http://www.ti.com/computers">www.ti.com/computers</a>                           |
| Consumer Electronics       | <a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>                   |
| Energy                     | <a href="http://www.ti.com/energy">www.ti.com/energy</a>                                 |
| Industrial                 | <a href="http://www.ti.com/industrial">www.ti.com/industrial</a>                         |
| Medical                    | <a href="http://www.ti.com/medical">www.ti.com/medical</a>                               |
| Security                   | <a href="http://www.ti.com/security">www.ti.com/security</a>                             |
| Space, Avionics & Defense  | <a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a> |
| Video and Imaging          | <a href="http://www.ti.com/video">www.ti.com/video</a>                                   |
| Wireless                   | <a href="http://www.ti.com/wireless-apps">www.ti.com/wireless-apps</a>                   |