







L712RA
CENTER PIN $\varnothing 0.098$
SCALE 3:1









L722RA
CENTER PIN $\varnothing 0.076$
SCALE 3:1



L732RA
CENTER PIN $\varnothing 0.048$
SCALE 3:1



CIRCUIT DIAGRAM



RECOMMENDED PANEL LAYOUT
(COMPONENT SIDE)

- NOTE:
1. FOR HAND INSERTION USE 0.130,
FOR AUTOMATED INSERTION USE 0.135.
 2. WASHER AND HEX NUT SHIPPED UNASSEMBLED.
 3. MATERIALS:
MOUNTING BUSHING - COPPER ALLOY, NICKEL PLATED
HOUSING - THERMOPLASTIC, BLACK
PIN, SPRING AND TERMINALS - COPPER ALLOY, SILVER PLATED
INSULATORS - PHENOLIC
HARDWARE (NOT SHOWN)
HEX NUT - COPPER ALLOY, NICKEL PLATED
FLAT WASHER - STEEL, NICKEL PLATED
 4. THESE PRODUCTS ARE RoHS COMPLIANT.

CUSTOMER DRAWING

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					UNLESS OTHERWISE SPECIFIED					SIZE				
					1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ± 0.01 - THREE PLACE DECIMALS ± 0.005 - ANGLES $\pm 1^\circ$ - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.					WIDTH				
					2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ± 0.002					MULT				
					3. REMOVE ALL BURRS					LBS/M				
					DO NOT SCALE DRAWING					TEMPER				
										FINISH				
										SPEC No.				
										MATERIAL				
										SPEC No.				
										FIRST USED ON				
										SCALE 3:1				
										DATE DRAWN				
										BY				
										CHKD				
										MM				
										APVD				
										JF				
										4-MAR-99				
										3-4-99				
										3-10-99				
										NAME				
										LONG BUSHING, RIGHT ANGLE				
										POWER JACK				
										PART No.				
										L7__RA__SERIES				
										REV				
										C				