


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		B	REDWN & REV; EC 0B40-0061-01	30MAR01	LH	GB
			C	REV-EC0-06-007951	05APR06	LH	GB
			D	REV EC0-10-011451	01JUN2010	LH	RA



RECOMMENDED MOUNTING DIMENSIONS



MOUNTING:

A)WALL: SINGLE OR DOUBLE GANG ELECTRICAL BOXES, FURNITURE PANELS, DESKS, SURFACE ACCESSIBLE RACEWAYS, FLAT SURFACE.

B)FLOOR: CELLULAR PRESETS OR POKE-THRUS, UNDERCARPET WIRING.

10. SHIPPING WEIGHT: 0.46 POUNDS PER ASSEMBLY.
11. TWO LABELS, LABEL COVER AND FOUR 6-32 X .88 [22.35] LONG SELF-TAPPING MOUNTING SCREWS ARE PACKAGED INSIDE MOUNT OUTLET ASSEMBLY.



DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.

2.

DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS.

3.

DESCRIPTION: A WORKSTATION OUTLET CAPABLE OF DISTRIBUTING COAX, FIBER, AND TWISTED PAIR. THE OUTLET CAN EASILY BE RECONFIGURED TO ACCOMODATE THE APPLICATION NEEDS.



MATERIAL: BASE, COVER, ICON WHEEL AND INSERTS - ABS MOLDING COMPOUND, 94V-0 RATED. SEE TABLE FOR COLOR. LABEL COVER - POLYCARBONATE MOLDING COMPOUND, CLEAR. SCREWS - ZINC PLATED CARBON STEEL. PRESS-IN INSERT - STAINLESS STEEL.

5.

FEATURES:

- A) ACCOMODATES FIBER OPTIC, COAXIAL, AND TWISTED PAIR MEDIA.
- B) EIGHT PORT INTERCHANGABLE INSERTS.
- C) SUPPORTS AMP NETCONNECT® SYSTEMS.
- D) CONTROLLED STORAGE FOR 2-3 FEET EACH OF TWO DUAL FIBER CABLES AT MINIMUM REQUIRED RADIUS.

6.


APPROVALS: N/A

7.

ELECTRICAL PARAMETERS: UL FILE E81956, CSA FILE LR7189.

8.

PACKAGING: ONE ASSEMBLY PER PRINTED POLYBAG.



INSERT  
8 REQUIRED

OBSOLETE	NEMA GRAY	557366-3
	LIGHT ALMOND	557366-1
	COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	L. HALL	28MAR01	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK	G. BOWMAN	30MAR01				
		APVD	G. BOWMAN	30MAR01	NAME			
		PRODUCT SPEC			SURFACE MOUNT OUTLET ASSEMBLY			
		APPLICATION SPEC			-			
		408-3281			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT			A2	00779	C=557366	-
		CUSTOMER DRAWING			SCALE	1:1	SHEET	1 of 1
					REV			