

Anderson Power Products® 1367G1
 Pneumatic crimp tool offers an industrial strength bridge between manually hand crimping and investing in a bench top press and applicator. This tool is manufactured in the U.S. and the jaws are constructed of high carbon hardened steel. This ensures that the customer receives a rugged, reliable tool that will provide the highest level of performance and accuracy available.

Features

- **Die set is designed specifically for APP contacts**

Provides crimps that meet or exceed UL standards

- **Integrated finger shield**

Provides increased safety for the operator

- **Contact Locator**

Assures proper crimp location and orientation

- **Removable stand**

Allows for portability in the factory or field



- **Optional accessories such as scissor and nipper attachment**

Increases the value of your tool

- **Tool operates at 80 to 100 psi, filtered and lubricated air**

Compatible with most air compressors

- **Pneumatic cylinder constructed of anodized aluminum and heat treated steel**

Offers durability


ORDERING INFORMATION

For Use With Contacts

Part Number	Description	AWG	Wire sq. mm
1331	Individual	12/16	3.3/1.3
1332	Individual	16/20	1.3/.52

Contacts

Part Number	-A- mm in.	-B- mm in.	-C- mm in.	-D- mm in.	-E- mm in.
1331	16.25	.64	7.87	.31	3.81 .15
1332	16.25	.64	7.87	.31	3.05 .12



Hand Tool

Part Number-New	Part Number-Old	Contacts	AWG	Wire sq.mm	Pullout Values (lbs) (per UL standard 486A)	Tool Cavities
1367G1	1353G1	1331	#12,14, 16	3.3/1.3	70, 50, 30	Cavity 30 #12, 14, 16 AWG

Crimp Height Data

Wire	Contact	Tolerance (+/- .005)
12	1331	0.101
14	1331	0.095
16	1331	0.095
16	1332	0.078
18	1332	0.075
20	1332	0.072

THE TOOL IS EQUIPPED WITH A RATCHET MECHANISM TO ASSURE RELIABLE CRIMP TERMINATIONS. A RATCHET RELEASE LEVER IS PROVIDED TO ALLOW FOR REMOVAL OF AN INCORRECTLY PLACED OR OVERSIZED CONTACT. ADJUST RATCHET RELEASE HANDLE FORCE TO 5-15 LBS.

All data subject to change without notice

DS-1367G1 REV02

HEADQUARTERS: 13 Pratts Junction Road, Sterling, MA 01564-2305 T:978-422-3600 F:978-422-3700

EUROPE: Rathfarnham Road, Fermoy Co. Cork, Ireland T:353-(0)25-32277 F:353-(0)25-32296

ASIA/PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T:852-2636-0836 F:852-2635-9036

CHINA: IDEAL Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou W. Ind. Par. Songgang Baoan District, Shenzhen, PR. China 51810 T: 86-755-2768-2118 F: 86-755-2768-2218

TAIWAN: IDEAL Anderson Asia Pacific Ltd., Taiwan Branch, 4F-2, No.116, Dadun 20th St., Situn District, Taichung City 407, Taiwan (R.O.C.) T: 886-4-2310-6451 F:886-4-2310-6460

www.andersonpower.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Anderson Power Products:](#)

[1367G1](#)