



DESCRIPTION: MALE - DIP SOLDER - MACHINED - ECONOMY



No. OF PINS	DIMENSIONS							
	A	B	C	D	E	F	G	H
9	1.213	0.984	0.666	0.329	0.236	0.756	0.496	0.427
	30.80	24.99	16.92	8.36	5.99	19.20	12.60	10.85
15	1.541	1.312	0.994	0.329	0.236	1.091	0.496	0.427
	39.15	33.32	25.25	8.36	5.99	27.70	12.60	10.85
25	2.087	1.852	1.534	0.329	0.236	1.618	0.496	0.427
	53.00	47.04	38.96	8.36	5.99	41.10	12.60	10.85

772-EYY-1 1 3 R YY 1

SERIES
POSITIONS
E09
E15
E25
GENDER
1 = MALE
TERMINATION
1 = DIP SOLDER
SHELL PLATING
3 = NICKEL (GROUND INDENTS)
RoHS COMPLIANT
HARDWARE OPTIONS
00 = NO HARDWARE
01 = 0.098" 4-40 INSERT, BOARD SIDE
05 = 0.224" 4-40 BOARD LOCK, BOARD SIDE
PLATING OPTIONS
1 = GOLD FLASH

MATERIAL:

SHELL: STEEL, NICKEL PLATED
INSULATOR: UL 94V-O RATED, WHITE PA6T
PROCESS TEMP.: 260° C
CONTACT: BRASS
SEALING MATERIAL: F08 FLEXIBLE ADHESIVE

MEETS IP67
STANDARDS

(SEE PAGE 3 FOR SEALING DETAILS)


ELECTRICAL:

CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: 15 mOhms Max.
INSULATION RESISTANCE: 1,000 MOhms min.
VOLTAGE: 500VAC FOR 1 MINUTE
TEMPERATURE: -50° C TO 100° C

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 9-18-08	
		CHECKED:		DATE:	
NorComp	SCALE: 1 : 1		SHEET 1		OF 3
	DWG NO. 772-EYY-113RYY1		REV 2		




HARDWARE OPTIONS

ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS

01X 0.098" (BOARD SIDE) - CN1



05X 0.224" BOARD SIDE - CN10



DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: C. SMITH		DATE: 06-10-09	
			CHECKED:		DATE:	
			SCALE: 2.5 : 1		SHEET 3 OF 3	
			DWG NO. 772-EYY-113RYY1		REV 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

<u>772-E09-113R001</u>	<u>772-E15-113R001</u>	<u>772-E25-113R001</u>	<u>772-E15-213R011</u>	<u>772-E15-113R011</u>	<u>772-E15-213R051</u>
<u>772-E15-113R051</u>	<u>772-E25-213R011</u>	<u>772-E25-113R011</u>	<u>772-E25-113R051</u>	<u>772-E25-213R051</u>	<u>772-E09-203R011</u>
<u>772-E25-103R011</u>	<u>772-E09-213R051</u>	<u>772-E09-113R051</u>	<u>772-E09-213R011</u>	<u>772-E09-113R011</u>	<u>772-E25-203R011</u>
<u>772-E15-103R011</u>	<u>772-E15-203R011</u>				