



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE 1-2	@20°C	0.350 ohms max.
D.C. RESISTANCE 3-4	@20°C	0.350 ohms max.
INDUCTANCE 1-2	10kHz, 100mVAC, Ls	30uH min.
DIELECTRIC 1-4	3750VAC, 1 second	3000VAC, 1 minute
URNS RATIO	(4-3):(1-2)	1.67:1, ±1%
SURGE TEST	6kV Peak	1.2 x 50uS

GENERAL SPECIFICATIONS:

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Supplementary insulation for a primary circuit at a working voltage of 250Vrms.

REV.	DATE
6B	10/09
6A	9/07

Packaging Specifications
Method: Tape & Reel
PKG-0748
www.midcom-inc.com

6B

Tolerances unless otherwise specified:
Angles: ±1° Decimals: ±.005 [.13]
Fractions: ±1/64 Footprint: ±.005 [.13]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE

TRANSFORMER

eiSos p/n: 750110007



DRAWING NO.

750110007

REVISIONS: SEE SHEET 1

SCALE ---

AGENCY NUMBER

UL CODE
FILE# E205930

BB

SHEET 2 OF 6