

SAI-8-F 4P FC 10M N**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Whereas the standard M12 system requires the sleeves to be laboriously screwed on and that operation is hindered by the vibration guard, M12 Push-Pull works with one click, just like those well-known garden hose systems. The audible locking function guarantees a safe and reliable connection as well as a good seal. The new SAI M12 Push-Pull distributors can be used with M12 plug-in connectors but also with the new M12 Push-Pull plug-in connectors.

General ordering data

Delivery status	Discontinued
Available until	2010-03-04
Type	SAI-8-F 4P FC 10M N
Order No.	1931940000
Version	Sensor-actuator passive distributor, Push-Pull, M12, Fixed cable version, 10 m, Yes
GTIN (EAN)	4032248581955
Qty.	1 pc(s).

Creation date August 18, 2020 2:46:49 AM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

SAI-8-F 4P FC 10M N

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Width	54 mm	Width (inches)	2.126 inch
Height	26 mm	Height (inches)	1.024 inch
Net weight	1,260 g		

Temperatures

Operating temperature range, max.	80 °C	Operating temperature range, min.	-25 °C
Operating temperature, max.	80 °C	Operating temperature, min.	-25 °C
Operating temperature	-25 - 80°C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Connection data

Sheathing stripping length	100 mm	Distributor outlet	Fixed cable version
----------------------------	--------	--------------------	---------------------

Standards

Certificate No. (cURus)	E92202
-------------------------	--------

Electrical data

Rated voltage, min.	10 V	Test voltage	1 kV
Max. current-carrying capacity per slot	4 A	Current per signal	2 A
Electrical isolation available	No	Insulation strength	10 ⁹ Ω

General technical data

Plug-in station coding	A	Protection degree	IP67
Number of poles	11	Number of contact sockets	8
Connection thread	M12	Pollution severity	3
Fire behaviour	V-0	LED	Yes
LED initiator	Yes	LED colour for indicating operation	green
LED colour for I/O function	yellow		

Material data

Housing main material	PA 6 GF	Material of distributor	Plastic
Housing colour	grey, RAL 7032	Screw socket	Nickel-plated CuZn
Contact material	CuZn	Contact surface	Gold-plated
Contact carrier material	PBT (UL 94 V0)		

Technical data cable

Cable length	10 m	Suitable for cable carriers	Yes
Number of poles		Wire cross section	8 x 0.34 mm ² + 3 x 1.0 mm ²
O.D.	8.2 mm	Shielded	No
Sheath material	PUR	Sheathing colour	black
Halogen	No	Bending radius, min., moving	10 x cable diameter
Bending cycles	2 Mio		

Creation date August 18, 2020 2:46:49 AM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

2

Data sheet

SAI-8-F 4P FC 10M N

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Classifications

UNSPSC 43-17-27-10

Approvals

Approvals



ROHS Conform