



PART NUMBER	REV	FIRST USED
1385224 -1	A	122500-1
1385224 -2	A	565435-5
1385224 -3	A	354500-1



TERMINAL NAME: PIN CONTACT									
AMP PN		MFR PN		JAE TERMINAL		CUST CRIMP SPECS			
286922		MX5-PW-PC1-5500		PAD LTR	CRIMP HEIGHT		WIRE SIZE		
				A	.041 ±.002 [1.04 ±0.05mm]		18		
				B	NOT		USED		
				C	NOT		USED		
				D	NOT		USED		
				CRIMP	SIZE	TYPE	RANGE		
				WIRE	.090 [2.29mm]	F	18		
				INSUL	.090 [2.29mm]	F	ø.080		
WIRE STRIP LENGTH		TERM APPL SPEC		FEED		APPL INSTRUCTION		SET UP GAGE	LAYOUT
.156-.188		NONE		.382		408-8040		458637-1	L2493

							129
							128
							127
2	2	2	-	C	4-354779-9	PIN, WIRE DISC (.3235)A	126
1	1	1	-	A	986950-1	WASHER, FLAT PRECISION	125
1	1	1	-	A	217238-1	GENERAL INSTRUCTION PACKAGE	124
1	1	1	-	-	4088040	SF APPL INST 408-8040	123
							122
1	1	1	-	A	4-21028-0	PIN,SLT SPR(Ø.093x.75)ST GDE PL	121
REF	REF	REF	-	A	1-21030-1	PIN,DOWEL (Ø.187x.50)LEVER	120
REF	REF	REF	-	A	1-21030-6	PIN,DOWEL (Ø.187x1.25)HOUSING	119
REF	REF	REF	-	A	21045-3	RING,RET "C"(Ø.187)FD FING PIN	118
1	1	1	-	A	21024-5	WASHER, LOCK (#10)ADJ BLOCK	117
REF	REF	REF	-	A	21024-5	WASHER,LOCK (#10)ADJ PLATE	116
REF	REF	REF	-	A	21024-5	WASHER,LOCK (#10)FEED GDE ROD	115
2	2	2	-	A	21024-2	WASHER,LOCK (#4)FRONT STP GUIDE	114
REF	REF	REF	-	A	5-21028-1	PIN,SLT SPR(Ø.125x.50)ADJ ROD	113
							112
4	4	4	-	A	21024-4	WASHER, LOCK (#8)STRIPPER	111
REF	REF	REF	-	A	21899-4	WASHER,FLAT (Ø5/16)SCREW ADJ	110
							109
1	1	1	-	A	21018-5	NUT, HEX (NO.6)HOLDDOWN	108
REF	REF	REF	-	A	21068-5	NUT, HEX (6-32)FEED ADJ	107
							106
							105
							104
1	1	1	-	A	21009-2	SCR,5KT SET(1/4-20x.25 LW)RAM	103
2	2	2	-	A	21017-2	SCR,DRIVE (#2x.19)ID PLATE	102
REF	REF	REF	-	A	6-23715-5	SCR,PAN HD (6-32x1.50)FEED ADJ	101
1	1	1	-	B	461264-1	PLATE, IDENTIFICATION	100
2	2	2	-	A	3-21002-0	SCR,BHC (10-32x.88)DRAG	99
1	1	1	-	A	22733-8	SCR,BHC (8-32x.38 LW)ANVIL	98
REF	REF	REF	-	A	2-21002-9	SCR,BHC (10-32x.75)CAP	97
REF	REF	REF	-	A	2-22733-8	SCR,BHC (1/4-20x.62)HOUSING	96
REF	REF	REF	-	A	2-21002-7	SCR,BHC (10-32x.50)SG ADJ BLOCK	95
6	6	6	-	A	2-21002-2	SCR,BHC (8-32x.50)TERM H DWN	94
							93
							92
1	1	1	-	A	1-21002-7	SCR,BHC (6-32x.38)CAM	91
							90
							89
							88
2	2	2	-	A	2-21000-8	SCR,SHC (8-32x.57)DEP-HOLD	87
1	1	1	-	A	2-22603-0	SCR,HEX HD (8-32x.31)FEED FINGER	86
2	2	2	-	A	1-21000-3	SCR,SHC (4-40x.25)F ST GUIDE	85
1	1	1	-	A	2-21000-7	SCR,SHC (8-32x.50)STRIPPER	84
REF	REF	REF	-	A	3-21000-7	SCR,SHC (10-32x.75)FEED ROD GD	83
REF	REF	REF	-	A	3-21000-6	SCR,SHC (10-32x.62)FD ADJ BLK	82
1	1	1	-	A	3-21000-4	SCR,SHC (10-32x.38)SG ADJ BL	81
REF	REF	REF	-	A	3-21000-4	SCR,SHC (10-32x.38)PIVOT BLK	80
-	REF	-	-	B	455749-1	GUARD, WINDOW	79
REF	-	-	-	B	679532-1	INSERT, GUARD	78
							77
							76
							75
1	1	1	-	A	690603-1	SPRING, ASSIST	74
1	1	1	-	A	23030-1	SCR,SHC (6-32x.25 SL)INS DISC	73
REF	REF	REF	-	A	458109-1	WASHER, SPECIAL	72
REF	REF	REF	-	A	690517-1	SPACER	71
-3	-2	-1	U/M	DWG SIZE	PART NO	DESCRIPTION	ITEM NO
QTY RECD PER ASSY				PARTS LIST			

-1			LEADMAKER		MECH POST FEED			
-2			BENCH MODEL K		MECH PRE FEED			
-3			BENCH MODEL G		MECH PRE FEED			
REF	REF	REF	-	B	22594-8	NUT, HEX (1/2-20)		70
REF	REF	REF	-	B	240628-1	PLATE, ADJUSTMENT		69
REF	REF	REF	-	B	240626-1	SHAFT, PIVOT		68
REF	REF	REF	-	B	240633-1	BUSHING		67
REF	REF	REF	-	A	455680-1	LEVER, INTERMEDIATE		66
REF	REF	REF	-	B	240629-1	BLOCK, PIVOT		65
REF	REF	REF	-	A	240632-2	SCREW, ADJ FEED ROD		64
REF	REF	REF	-	B	240659-3	PIN, CAM ROLLER		63
REF	REF	REF	-	B	240658-1	ROLLER, CAM		62
REF	REF	REF	-	B	454398-2	ROD, FEED		61
REF	REF	REF	-	A	454178-1	GUIDE, FEED ROD		60
REF	REF	REF	-	C	454220-1	CAP, RAM		59
REF	REF	REF	-	D	454485-1	HOUSING		58
								57
1	1	1	-	B	690542-2	PAWL, FEED		56
REF	REF	REF	-	B	240624-1	PIN, FEED FINGER		55
REF	REF	REF	-	B	691499-1	SPRING, FEED FINGER		54
REF	REF	REF	-	B	690541-1	HOLDER, FEED FINGER		53
REF	REF	REF	-	A	455679-1	LEVER, TERMINAL FEED ARM		52
1	1	1	-	A	811242-2	BUMPER, HOLDDOWN		51
1	1	1	-	A	690753-1	SPACER, TONKER		50
1	-	-	-	B	690602-6	CAM, PRE-FEED 1 5/8 ST		49
-	1	-	-	B	690602-5	CAM, PRE-FEED 1 1/8 ST		48
-	-	1	-	B	690501-4	CAM, POST-FEED 1 5/8 ST		47
1	1	1	-	B	459456-1	APPLICATOR, BASIC (SUBASSY)		46
1	1	1	-	A	690191-1	PLUG, NYLON		45
1	1	1	-	C	455673-1	RAM		44
1	1	1	-	A	690125-1	WASHER, LAMINATED		43
1	1	1	-	A	690124-1	WASHER, RAM		42
1	1	1	-	A	7-21002-9	BOLT, CRIMPER (5/16x1.00)		41
1	1	1	-	A	23241-6	BALL, STEEL		40
1	1	1	-	A	690170-1	SPRING, COMPRESSION		39
1	1	1	-	C	690142-1	DISC, INSULATION		38
1	1	1	-	D	354777-1	WIRE DISC, PLASTIC		37
1	1	1	-	A	22480-5	WASHER, SPRING		36
1	1	1	-	B	690212-1	POST, RAM		35
1	1	1	-	B	690786-6	SUPPORT, TERMINAL		34
REF	REF	REF	-	D	455675-1	PLATE, BASE		33
1	1	1	-	A	690432-3	SCREW, ADJUSTMENT		32
								31
REF	REF	REF	-	B	455689-1	BLOCK, STRIP GUIDE ADJ		30
1	1	1	-	C	455671-1	PLATE, STRIP GUIDE		29
1	1	1	-	C	1-455888-0	SPACER, FRONT SHEAR DEP		28
2	2	2	-	A	1-22284-0	SPRING, DRAG		27
1	1	1	-	B	690546-1	LEVER, DRAG RELEASE		26
1	1	1	-	B	240792-1	DRAG, TERMINAL		25
1	1	1	-	D	6-690504-6	GUIDE, STRIP (REAR)		24
1	1	1	-	A	690438-1	GUIDE, STRIP (FRONT)		23
								22
REF	REF	REF	-	A	4-22284-9	SPRING, FEED RETURN		21
								20
1	1	1	-	B	690472-9	STRIPPER		19
								18
								17
1	1	1	-	B	318563-1	GUARD, CHIP, FRONT		16
								15
								14
								13
1	1	1	-	A	5-22280-0	SPRING, SHEAR		12



- | | | |
|---|---|---|
| 1 | RECOMMENDED SPARE PARTS. | |
| 2 | GREASE LIGHTLY. | |
| 3 | GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE. | F |
| 4 | LUBRICATE DAILY USING NO. 20 MACHINE OIL. | F |
| 5 | ITEMS WITH QTY OF REF SPECIFIED (EXCEPT ITEMS 78 AND 79) ARE USED ON ITEM 46. | |
| 6 | CUT TO LENGTH AT ASSY | |
| 7 | GUIDE ON INSULATION BARREL. | |
| 8 | POSITION BETWEEN WIRE AND INSULATION CRIMPERS. | |