

ITEM KEY	SIGNAL DATA			
	SIZE 4 x 45		TOTAL NO. OF POSITIONS -180	NO. OF POSITIONS LOADED - 180
	PLATING-30u"/.76u AU DUPLEX		R/A SOLDER TAIL STYLE	
	PIN P/N	QTY.	MATING LENGTH	TAIL LENGTH
A	94523-A101B	45	.220 / 5.89	.100 / 2.54
B	94523-A102B	45	.220 / 5.89	.100 / 2.54
C	94523-A103B	45	.220 / 5.89	.100 / 2.54
D	94523-A104B	45	.220 / 5.89	.100 / 2.54

HSG P/N: 50798-X180X

A

PLORICIE


	1	5	10	15	20	25	30	35	40	45	
D	D	D	D	D	D	D	D	D	D	D	D
C	C	C	C	C	C	C	C	C	C	C	C
B	B	B	B	B	B	B	B	B	B	B	B
A	A	A	A	A	A	A	A	A	A	A	A

B

PIN
1

A

B



Copyright FCI
FCIconnect.com

1. ALL POSITIONS ARE LOADED.
2. COLUMN 1, ROW A IS DESIGNATED AS SIGNAL PIN 1, AS VIEWED FROM THE MATING FACE.
3. FOR ADDED DIMENSIONAL INFORMATION REFER TO DOCUMENT NUMBER "50119".
4. GUIDE PIN "78628-002" INSTALLED IN BOTH ENDS OF ASSEMBLY (W/ "94522-002" S.S. SCREW THRU BRACKET "50345-001") PER ABOVE APPLICATION VIEW.
5. RETENTION CLAW 50890-001 WILL BE INSTALLED ON BOTH ENDS.

mat'l. code		surface		tolerance ISO 1302 ✓ ISO 1101	projection	product family
ltr	ecn no	dr	date			
A	V81486	HTB	9/3/98	.XX ±.01	—	HPC
B	V01590	JWS	8/1/00	.XXX ±.005	↔	title
C	M06-0280	MHT	7/22/06	σ±2°	scale 1:1	4 ROW R/A HEADER, DUPLEX S.T.B. PINS, SELECT LOAD, 0 G.P.
				XXXX ±.0020		dwg no sheet 1 of 1 size
						50782-XX001 A3
						type Product Customer Drawing
sheet		revision	C			
index		sheet	1			