





REV.	DATE	DESCRIPTION
NC	03/06/00	INITIAL RELEASE
A	12/12/05	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .178"
2. CONTACT PIN TO SOLDER.

8				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
7			1		DRAWN	G.R.S.					12/12/05	
6					CHECKED			PART DESCRIPTION MINI 75ohm SMB CRIMP PLUG (FOR AT&T 735A CABLE)				
5					ISSUED							
4	FERRULE	BRASS	GOLD			SHEET	1 OF 1		PART NO. 142222-75			
3	CONTACT PIN	BER. COPPER	GOLD	1								
2	INSULATOR	TEFLON	NATURAL	1					DWG. NO. 142222-75.DWG REV. A SIZE A SCALE NA			
1	BODY	BRASS	GOLD	1								
DESCRIPTION		MATERIAL	FINISH	QTY			CAD FILE C:/142/142222-75.DWG					