





- 1 HOUSING MATERIAL: LIQUID CRYSTAL POLYMER PER ASTM D5138 LCP000 G30A 32250, COLOR: NATURAL.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3 CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL.
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA UNCONTROLLED ENVIRONMENT.
ON LEADS
0.0006 MIN TIN-LEAD OVER UNDERPLATE.
LUBRICATION (ENTIRE CONTACT):
SURFACE CONDITIONER PER AMP SPEC 112-1002 AFTER PLATING.
- 4 PART MARKING PER AMP INCORPORATED SPECIFICATION 115-9009, LOCATED APPROXIMATELY AS SHOWN.
- 5 DIMENSION APPLIES WHEN SEATED ON PRINTED CIRCUIT BOARD.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



OBSOLETE	4.25	34	17	35.88	3	72	1-536504-2
3	4.25	130	65	131.88	3	264	1-536504-1
OBSOLETE	4.25	106	53	107.88	3	216	1-536504-0
6 OBSOLETE	4.25	118	59	119.88	3	240	536504-9
OBSOLETE	4.25	70	35	71.88	3	144	536504-8
OBSOLETE	4.25	66	33	67.88	3	136	536504-7
OBSOLETE	4.25	58	29	59.88	3	120	536504-6
6 OBSOLETE	4.25	82	41	83.88	3	168	536504-5
OBSOLETE	4.25	94	47	95.88	3	192	536504-4
	4.25	46	23	47.88	3	96	536504-3
	4.25	22	11	23.88	3	48	536504-2
OBSOLETE	4.25	10	5	11.88	3	24	536504-1
	D	C	B	A	FINISH	NO OF POSN	PART NUMBER

RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.R.BENDER 10/27/92	TE Connectivity	
DIMENSIONS: INCHES		CHK D.BAECHTLE 02/18/93	NAME PIN ASSEMBLY, SIGNAL MODULE, Z-PACK 2mm FB, 2mm	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$.13 3 PLC $\pm$ - 4 PLC $\pm$ - ANGLES $\pm$ -		PRODUCT SPEC - APPLICATION SPEC -	SIZE A1	
MATERIAL 1		WEIGHT -	00779 536504	
FINISH 3		CUSTOMER DRAWING		
SCALE 4:1		SHEET 1 of 1		REV V