


VECTORBORD® CIRCBORD™ PART NO. : 8007



Description :

4.5" x 6.50", Hole Dia.: 0.042", Grid: 0.100" x 0.100"

Pad-Per-Hole pattern on component side.

Overall Ground Plane pattern on wiring side and holes not plated through.

0.080" dia. isolated solder pad around holes on component side

Accommodates any type DIP IC device or discrete

Plane surfaces solder-coated for user convenience

To commit wire-wrap pins to voltage and ground planes, use Vector: T124 solder washers

Vector: T124 solder washers available separately

Circuit Pattern :	Pad-Per-Hole & Ground Plane
Contacts :	N/A
16 Pin DIP Capacity :	60
Hole Diameter :	0.042" { 1.0668 mm }
Grid :	0.100" x 0.100" { 2.54mm X 2.54mm }
Dimension { H, W, T } :	4.50" x 6.50" x 0.062"
Material :	CEM-1
Wire-Wrap Terminals :	T44, T46, T49, T68
Solder Terminals :	T42-1
Wire-Wrap Socket Pins :	R32
NEMA Grade :	CEM-1
UL Flammability Class :	94V - 0