


Adapter Sub-D 37 Pin Buchse > Terminalblock 39 Pin

Kurzbeschreibung

Dieser Sub-D zu Terminalblock Adapter ist für spezielle Industrieanwendungen geeignet, wie z.B. zum Anschluss einzelner Kabelstränge mit offenen Kabelenden. Anwendung findet der Adapter beispielsweise im Hobbybereich, wie Eisenbahnmodellbau.

Abbildungen



Art.	65319
EAN	4043619653195
Ursprungsland	China
Zolltarifnummer	84718000

Technische Daten

- Sub-D 37 Pin Buchse
- 3 x 13 Pin Terminalblock (37 Pins beschaltet)
- Pitch 3.81 mm
- Buchse mit Muttern
- Maße (LxBxH): 69,7 mm x 69,32 mm x 16,05 mm

Packungsinhalt

- Adapter

Verpackung

- Delock Poly Bag


Adapter Sub-D 37 pin female

> Terminal Block 39 pin

Description

This Sub-D to terminal block adapter is made for special industrial application e.g. for connecting single wires with open cable heads. It also can be used in the hobby area for example for model railroading.

Images



Ref.	65319
EAN	4043619653195
Country of origin	China
Customs tariff number	84718000

Specification

- Sub-D 37 pin female
- 3 x 13 pin terminal block (37 pins connected)
- Pitch 3.81 mm
- Female port with screw nuts
- Dimension (LxWxH): 69.7 mm x 69.32 mm x 16.05 mm

Package content





- Adapter

Package

- Delock poly bag

WIRING TABLE	
DB37 PIN #	TERMINAL PIN #
1	1
2	2
3	3
4	4
5	5
6	6
.....	
.....	
.....	
32	32
33	33
34	34
35	35
36	36
37	37
SHELL	SHL

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	7/11/11	Liu Jian Ping



Part name:
Adapter terminal block > Sub-D 37 pin female

Electrical Character:

- 1> 100% open&short testing
- 2> With understanding voltage:DC 500 V 0.01 Sec.
- 3> Insulation Resistance: 50M Ohm (Min)
- 4> Conductive Resistance: 2 Ohm(Max)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN mm	APPROVALS	DATE	DELOCK® we move the world
	DRAWN BY May	7/11/2011	
	CHECKED BY Gang	7/11/2011	
	APPROVED BY Steven	7/12/2010	
DIMENSIONAL TOLERANCES:	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		Item no.
.X = ±0.3 .XX = ±0.2 .XXX = ±0.1			65319
ANGULAR TOLERANCES:	PROJECTION		Barcode: 4043619653195
ALL = ± 1°			File: 88072
COLOR VARIATIONS MAY OCCUR			