

DM74ALS273

Octal D-Type Edge-Triggered Flip-Flop with Clear

General Description


These monolithic, positive-edge-triggered flip-flops utilize TTL circuitry to implement D-type flip-flop logic with a direct clear input.

Information at the D inputs meeting the setup requirements is transferred to the Q outputs on the positive-going edge of the clock pulse. Clock triggering occurs at a particular voltage level and is not directly related to the transition time of the positive-going pulse. When the clock input is at either the high or low level, the D input signal has no effect at the output.

Features

- Switching specifications at 50 pF
- Switching specifications guaranteed over full temperature and V_{CC} range
- Buffer-type outputs and improved AC offer significant advantage over 'LS273.
- Advanced oxide-isolated, ion-implanted Schottky TTL process
- Functionally and pin-for-pin compatible with 'LS273.

Connection Diagram



Order Number DM74ALS273WM,
DM74ALS273N, DM74ALS273SJ or DM74ALS273MSA
See Package Number M20B, M20D, MSA20 or N20A

DM74ALS273 Octal D-Type Edge-Triggered Flip-Flop with Clear

Absolute Maximum Ratings (Note 2)

Supply Voltage	7V
Input Voltage	7V
Operating Free Air Temperature Range	0°C to +70°C
DM74ALS	

Storage Temperature Range

-65°C to +150°C

Typical θ_{JA}

N Package

60.0°C/W

M Package

79.0°C/W

Recommended Operating Conditions

Symbol	Parameter	DM74ALS273			Units
		Min	Nom	Max	
V_{CC}	Supply Voltage	4.5	5	5.5	V
V_{IH}	High Level Input Voltage	2			V
V_{IL}	Low Level Input Voltage			0.8	V
I_{OH}	High Level Output Current			-2.6	mA
I_{OL}	Low Level Output Current			24	mA
f_{CLK}	Clock Frequency	0		35	MHz
$t_{W(CLK)}$	Width of Clock Pulse	High	14		ns
		Low	14		ns
t_W	Width of Clear Pulse	Low	10		ns
t_{SU}	Data Setup Time (Note 3)	10↑			ns
	Clear Inactive	15↑			
t_H	Data Hold Time	0↑			ns
T_A	Free Air Operating Temperature	0		70	°C

Note 1: This product meets application requirements of 500 temperature cycles from -65°C to +150°C.**Note 2:** The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the "Electrical Characteristics" table are not guaranteed at the absolute maximum ratings. The "Recommended Operating Conditions" table will define the conditions for actual device operation.**Note 3:** The (↑) arrow indicates the positive edge of the Clock is used for reference.**Electrical Characteristics**over recommended operating free air temperature range. All typical values are measured at $V_{CC} = 5V$, $T_A = 25^\circ C$.

Symbol	Parameter	Conditions	Min	Typ	Max	Units
V_{IK}	Input Clamp Voltage	$V_{CC} = 4.5V$, $I_I = -18\text{ mA}$			-1.5	V
V_{OH}	High Level Output Voltage	$V_{CC} = 4.5V$	$I_{OH} = -2.6\text{ mA}$	2.4	3.3	V
		$V_{CC} = 4.5V$ to $5.5V$	$I_{OH} = -400\text{ }\mu A$	$V_{CC} - 2$		V
V_{OL}	Low Level Output Voltage	$V_{CC} = 4.5V$	$I_{OL} = 12\text{ mA}$	0.25	0.4	V
			$I_{OL} = 24\text{ mA}$	0.35	0.5	V
I_I	Input Current @ Max. Input Voltage	$V_{CC} = 5.5V$, $V_{IH} = 7V$			0.1	mA
I_{IH}	High Level Input Current	$V_{CC} = 5.5V$, $V_{IH} = 2.7V$			20	μA
I_{IL}	Low Level Input Current	$V_{CC} = 5.5V$, $V_{IL} = 0.4V$			-0.2	mA
I_O	Output Drive Current	$V_{CC} = 5.5V$	$V_O = 2.25V$		-112	mA
I_{CC}	Supply Current	$V_{CC} = 5.5V$	Outputs High	11	20	mA
		Outputs Open	Outputs Low	19	29	mA

Switching Characteristics

over recommended operating free air temperature range. (Note 4)

Symbol	Parameter	Conditions	From	To	DM74ALS273		Units
					Min	Max	
f_{MAX}	Maximum Clock Frequency	$V_{CC} = 4.5V$ to $5.5V$			35		MHz

Switching Characteristics (Continued)

over recommended operating free air temperature range. (Note 4)

Symbol	Parameter	Conditions	From	To	DM74ALS273		Units
					Min	Max	
t_{PHL}	Propagation Delay Time High to Low Level Output	$R_L = 500\Omega$ $C_L = 50 \text{ pF}$	Clear	Any Q	4	18	ns
t_{PLH}	Propagation Delay Time Low to High Level Output		Clock	Any Q	2	12	ns
t_{PHL}	Propagation Delay Time High to Low Level Output		Clock	Any Q	3	15	ns

Note 4: See Section 1 for test waveforms and output load.


Function Table


(Each Flip-Flop)

Inputs			Output Q
Clear	Clock	D	
L	X	X	L
H	↑	H	H
H	↑	L	L
H	L	X	Q_0


L = Low State, H = High State, X = Don't Care
 ↑ = Positive Edge Transition, Q_0 = Previous Condition of Q

Logic Diagram







Physical Dimensions inches (millimeters) unless otherwise noted




S.O. Package (M)
Order Number DM74ALS273WM
Package Number M20B



Small Outline Package (SJ)
Order Number DM74ALS273SJ
Package Number M20D

Physical Dimensions inches (millimeters) unless otherwise noted (Continued)

Molded Shrink Small Outline Package (MSA)
Order Number DM74ALS273MSA
Package Number MSA20



Molded Dual-In-Line Package (N)
Order Number DM74ALS273N
Package Number N20A