






PRODUCT NO.	EMPTY POSITIONS
10031089-004LF	1, 2, 23, 24
10031089-005LF	23, 24
10031089-006LF	---



NOTES :

- MATERIAL :
HOUSING : HIGH TEMPERATURE PLASTIC.
TERMINAL : COPPER ALLOY
PLATING : GOLD FLASH OVER NICKEL PLATING.
- COMPRESSION FORCE : 110gf MIN AT 3.86mm FROM BASE.
- DURABILITY : 15 CYCLES
- THIS CUSTOMIZED PRODUCT IS MANUFACTURED ACCORDING TO THE CUSTOMER'S DRAWING AND SPECIFICATIONS. APPROACH MARKETING FOR ENQUIRIES.
- ALL DIMENSIONS ARE FOR REFERENCE PURPOSE ONLY. DRAWING IS SUBJECTED TO CHANGE WITHOUT NOTICE.
- PACKAGING : TAPE-AND-REEL
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.



mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family		
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title COMPRESSION CONNECTOR, 20/22/24 CONTACTS		
A	S06-0215	LTS	23JUN06	angles	linear				
				---		scale 5 : 1			
				dr	L T Soh	23JUN06	dwg no 10031089		
				enr	L T Soh	23JUN06			
				chr	L T Soh	23JUN06	type CUSTOMER Drawing		
				appd	JOEY NG	23JUN06			
sheet index	revision sheet								