



Copyright FCI.



FCIconnect.com



1 | 2

3 |

4

PRODUCT NUMBER

20020110-XXXXXXLF

20020110-□□□□A□□LF

PITCH

C: 3.50 mm  
D: 3.81 mm  
G: 5.00 mm  
H: 5.08 mm

POLES

02: 2 POLES  
03: 3 POLES  
04: 4 POLES  
|  
24: 24 POLES

LF : DENOTED RoHS COMPATIBLE

1 : STANDARD PRODUCT  
W/ BOX PACKING

PROPERTY TABLE

FCI SERIES NAME		06-350	06-381	06-500	06-508
PITCH (mm)		3.50	3.81	5.00	5.08
VOLTAGE RATING (VAC)		300	300	300	300
CURRENT RATING (A)	cULus	10	10	12	12
	VDE	10.5	10.5	NA	NA
WITHSTANDING VOLTAGE (kV)	cULus	1.6	1.6	1.6	1.6
	VDE	2.5	2.5	NA	NA
OPERATING TEMP. (°C)		-40~+115	-40~+115	-40~+115	-40~+115
SOLDERING TEMP. (°C)		250±10 (5 sec.)	250±10 (5 sec.)	250±10 (5 sec.)	250±10 (5 sec.)
POLES AVAILABLE		02~24	02~24	02~24	02~24
SAFETY CERTIFICATE					

HOUSING CODE

CODE	COLOR	AVAILABILITY
1	GREEN(RAL 6018/T)	STANDARD
2	BLACK	ON REQUEST ONLY
3	GREY(RAL 7004/P)	ON REQUEST ONLY
4	BLUE(RAL 5015/A)	ON REQUEST ONLY




## NOTES:

## MATERIALS


- 1-1 HOUSING: THERMALPLASTIC RESIN, UL 94V-0 RATED.
- 1-2 TERMINAL: COPPER ALLOY, TIN PLATED.
2. PRODUCTION SPECIFICATION REFER TO FCI GS-12-625.
3. BOXED PACKAGING.  
DETAILED PRODUCT PACKING SPECIFICATION REFER TO FCI GS-14-1394.
4. FCI, SAFETY CERTIFICATE LOGO AND SERIES NAME TO BE SHOWN ON PRODUCT SURFACE.
5. THE PRODUCTS WHERE THE PART NUMBER END IN "LF" MEET THE EUROPEAN UNION DIRECTIVE AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
6. RECOMENDED SOLDERING PROCESS BY WAVE SOLDER.

mat'l. code				surface	tolerance	projection	product family
				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK
litr	ecr no	dr	date	tolerances unless otherwise specified			title
H	T10-0193	WL	122310	angles	X.±0.5[.020]		TERMINAL BLOCK
J	T11-0013	WL	040811	to	X.X±0.3[.012]		PLUGGABLE SOCKET, RIGHT ANGLE
K	T-004746	WL	072011	X'±1"	X.XX±0.1[.004]		sheet 1 of 5 size
				dr	BEER FU	062509	20020110
				enr	BEER FU	062509	A4
				chr	GARY HSIEH	062509	type
				appd	JOSEPH HSIA	062509	CUSTOMER Drawing
sheet index	revision	K	K	K	K	K	
	sheet	1	2	3	4	5	

PRODUCT NUMBER	SERIES NAME	PITCH
20020110-CXXXXXXLF	06-350	3.50 mm



SECTION P-P



RECOMMENDED P.C.B LAYOUT




N= NUMBER OF POLES  
DIMENSION

Dim A	$(N-1) \times 3.5 [.138] + 4.9 [.193]$
Dim B	$(N-1) \times 3.5 [.138]$
Dim C	$(N-1) \times 3.5 [.138]$


Poles	Tolerance
2P-6P	$\pm 0.15 [.006]$
7P-12P	$\pm 0.20 [.008]$
13P-18P	$\pm 0.25 [.010]$
19P-24P	$\pm 0.30 [.012]$

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
K				angles	$X \pm 0.5 [.020]$	MM	TERMINAL BLOCK
					$X.X \pm 0.3 [.012]$	INCH	PLUGABLE, SOCKET, SIGNAL, R/A
				$X \pm 1"$	$X.XX \pm 0.1 [.004]$	scale	dwg no
				dr	BEER FU	062509	sheet 2 of 5
				enr	BEER FU	062509	size
				chr	GARY HSIEH	062509	A4
				appd	JOSEPH HSIA	062509	type
sheet index	revision sheet						CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020110-DXXXXXXLF	06-381	3.81 mm



RECOMMENDED P.C.B LAYOUT



SECTION P-P





N= NUMBER OF POLES  
DIMENSION

Dim A	$(N-1) \times 3.81 [0.150] + 5.0 [0.197]$
Dim B	$(N-1) \times 3.81 [0.150]$
Dim C	$(N-1) \times 3.81 [0.150]$

Poles	Tolerance
2p-6p	$\pm 0.15 [0.006]$
7p-12p	$\pm 0.20 [0.008]$
13p-16p	$\pm 0.25 [0.010]$
17p-24p	$\pm 0.30 [0.012]$

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection MM INCH	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
K				angles	$X \pm 0.5 [0.020]$	MM INCH	TERMINAL BLOCK PLUGABLE, SOCKET, SIGNAL, R/A
				$X \pm 1^\circ$	$X.X \pm 0.3 [0.012]$	scale	dwg no
					$X.XX \pm 0.1 [0.004]$		20020110
				dr	BEER FU	062509	sheet 3 of 5
				enr	BEER FU	062509	A4
				chr	GARY HSIEH	062509	type
				appd	JOSEPH HSIA	062509	CUSTOMER Drawing
sheet index	revision	sheet					

PRODUCT NUMBER	SERIES NAME	PITCH
20020110-GXXXXXXLF	06-500	5.00 mm



RECOMMENDED P.C.B LAYOUT





N = NUMBER OF POLES  
DIMENSION

Dim A	$N \times 5.0[.197] + 2.0[.193]$
Dim B	$(N-1) \times 5.0[.197]$
Dim C	$(N-1) \times 5.0[.197]$

Poles	Tolerance
2p-6p	$\pm 0.15[.006]$
7p-12p	$\pm 0.25[.010]$
13p-16p	$\pm 0.35[.014]$
17p-24p	$\pm 0.40[.016]$

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK
ltr	ecn	no	dr	tolerances unless otherwise specified			title
K				angles	$X \pm 0.5[.020]$	MM INCH	TERMINAL BLOCK PLUGABLE, SOCKET, SIGNAL, R/A
				$X \pm 1^\circ$	$X.X \pm 0.3[.012]$	scale	dwg no
				dr	BEER FU 062509	FCI	sheet 4 of 5
				enr	BEER FU 062509		20020110
				chr	GARY HSIEH 062509		A4
				app	JOSEPH HSIA 062509		type
sheet index	revision	sheet					CUSTOMER Drawing

PRODUCT NUMBER	SERIES NAME	PITCH
20020110-HXXXXXL	06-508	5.08 mm



RECOMMENDED P.C.B LAYOUT

N = NUMBER OF POLES  
DIMENSION

Dim A	$N \times 5.08 [.200] + 2.0 [.193]$
Dim B	$(N-1) \times 5.08 [.200]$
Dim C	$(N-1) \times 5.08 [.200]$

Poles	Tolerance
2p-6p	$\pm 0.15 [.006]$
7p-12p	$\pm 0.25 [.010]$
13p-16p	$\pm 0.35 [.014]$
17p-24p	$\pm 0.40 [.016]$

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM INCH	title
K				angles	$X \pm 0.5 [.020]$ $X.X \pm 0.3 [.012]$ $X \pm 1$		TERMINAL BLOCK PLUGABLE, SOCKET, SIGNAL, R/A
					$X.XX \pm 0.1 [.004]$	scale	dwg no 20020110
		dr	BEER FU	062509		FCI	sheet 5 of 5 size A4
		enr	BEER FU	062509			
		chr	GARY HSIEH	062509			
		appd	JOSEPH HSIA	062509			
sheet index	revision sheet						type CUSTOMER Drawing