




MATERIAL


stem-polypropylene, white
 nut-polypropylene, white
 float-polypropylene, white
 seal to side wall of reservoir-NBR, black
 Schaft-Polypropylen, weiss
 Mutter-Polypropylen, weiss
 Schwimmer-Polypropylen, weiss
 Montagedichtung zur Behälterseitenwand-NBR, schwarz

CABLE

round cable LIYY AWG26, grey
 UL-Style 2464
 colour of wires: white and braun
 Rundkabel LIYY AWG26, grau
 UL-Style 2464
 Adernfarben: weiss und braun

MARKING

MEDER, Type,
 Production code EN60062/
 factory code
 MEDER, Typ,
 Produktionscode EN60062/
 Fertigungsstätte



tolerances according to DIN ISO 2768 m



Products for tomorrow...

Europe: +49 / 7731 8399 0 | Email: info@meder.com
USA: +1 / 508 295 0771 | Email: salesusa@meder.com
Asia: +852 / 2955 1682 | Email: salesasia@meder.com

Item No.:
9534197314
Item:
LS03/DL-PP-BV97314
3000W

Special Product Data	Conditions	Min	Typ	Max	Unit
Contact rating	Any DC combination of V & A not to exceed their individual max.'s			10	W
Switching voltage	DC or Peak AC			180	V
Carry current	DC or Peak AC			1,25	A
Switching current	DC or Peak AC			0,5	A
Sensor-resistance	measured with 40% overdrive Sensor deactivated			1.000	mOhm
Housing material		PP			
Case colour		white			
Sealing compound		Polyurethan			

Environmental data	Conditions	Min	Typ	Max	Unit
Operating temperature	cable not moved	-30		80	°C
Operating temperature	cable moved	-5		80	°C
Storage temperature		-30		80	°C
Safety class	DIN EN 60529	IP68			

Cable specification	Conditions	Min	Typ	Max	Unit
Cable type		round cable, UL-Style 2464			
Cable material		PVC			
Cross section		AWG 26			

General data	Conditions	Min	Typ	Max	Unit
Mounting advice		over 5m cable, a resistor is recommended.			
Tightening torque				1	Nm

Modifications in the sense of technical progress are reserved

Designed at: 20.08.09 Designed by: WKOVACS
Last Change at: 01.02.12 Last Change by: WKOVACS

Approval at: 20.08.09 Approval by: DKUECHLER
Approval at: 01.02.12 Approval by: DKUECHLER

Version: 03