

Ordering number **C12607_VIRPI-S**


Family	Virpi	FWHM	15 degrees
Type	Lens array	Efficiency	94 %
LED	XT-E	cd/lm	7.160
Color	Clear	Gerber File	Available
Diameter	74.9 x 74.9 mm		
Height	9.4 mm		
Style	Square		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		

Ordering number **C12608_VIRPI-M**

Family	Virpi	FWHM	29 degrees
Type	Lens array	Efficiency	91 %
LED	XT-E	cd/lm	2.620
Color	Clear	Gerber File	Available
Diameter	74.9 x 74.9 mm		
Height	9.4 mm		
Style	Square		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		

Ordering number **C12609_VIRPI-W**

Family	Virpi	FWHM	41 degrees
Type	Lens array	Efficiency	90 %
LED	XT-E	cd/lm	1.680
Color	Clear	Gerber File	Available
Diameter	74.9 x 74.9 mm		
Height	9.4 mm		
Style	Square		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	Ready		



NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.

GENERAL INFORMATION

- Product series especially designed & optimized for XT-E series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:




http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%208N%20UL94_Yellow%20Card.pdf
<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%208N%20PLEXIGLAS-Datasheet.pdf>

D



C

B

A



Detail A
Scale: 2:1



Material:

- PMMA

Tolerances if not otherwise shown:

According to DIN ISO 2768-1

Linear measures:

Up to 30mm class F, otherwise class M.

According to DIN ISO 2768-2

Form and position:

class K

This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.



DRAWING TITLE

Ledil Oy
Salorankatu 10
FIN 24240 SALO
Finland

Datasheet Virpi series

DRAWN BY
pl

DATE
20.02.2012

SIZE
A4

DRAWING NUMBER

-

REV
1

CHECKED BY

DATE

DESIGNED BY
PL

DATE
03.02.2012

SCALE
1:1

WEIGHT(g)


SHEET
1/1

D

A


LEDiL Oy C12607_VIRPI-S_(XT-E) Eff.94.2% / LDC (Linear)

Luminaire: LEDiL Oy C12607_VIRPI-S_(XT-E) Eff.94.2%
Lamps: 1 x XT-E_5x5 (2100lm@250mA)




LEDiL Oy C12608_VIRPI-M_(XT-E) Eff.91.0% / LDC (Linear)

Luminaire: LEDiL Oy C12608_VIRPI-M_(XT-E) Eff.91.0%
Lamps: 1 x XT-E_5x5 (2049.85lm@250mA)




Luminaire: LEDiL Oy C12609_VIRPI-W_(XT-E) Eff.89.96%
Lamps: 1 x XT-E_VIRPI_5x5 (2119.89lm@250mA)



LEDiL Oy C12607_VIRPI-S_(XT-E) Eff.94.2% / LDC (Polar)

Luminaire: LEDiL Oy C12607_VIRPI-S_(XT-E) Eff.94.2%


Lamps: 1 x XT-E_5x5 (2100lm@250mA)



LEDiL Oy C12608_VIRPI-M_(XT-E) Eff.91.0% / LDC (Polar)

Luminaire: LEDiL Oy C12608_VIRPI-M_(XT-E) Eff.91.0%

Lamps: 1 x XT-E_5x5 (2049.85lm@250mA)



Luminaire: LEDiL Oy C12609_VIRPI-W_(XT-E) Eff.89.96%
Lamps: 1 x XT-E_VIRPI_5x5 (2119.89lm@250mA)

